## Capped 18-24 AWG: WTB

## 9176-700





The market and applications for simple and reliable discrete Wire-to-Board connectors continue to evolve. AVX first introduced the 9176 series of surface mountable Insulation Displacement Connectors (IDC) in 2007. Developed for harsh industrial and automotive applications, these connectors have been used in hundreds of applications from today's "Smart Meter" all the way down to a simple sensor termination to a PCB. Size and performance has been one of the key factors for selecting this connector in terminating 18-24AWG wires to a PCB.

The next generation of IDC connector moves beyond all of the technical and performance attributes to address the "User Friendliness" of the product. By changing the insulator from acting as a connector body and make it more like a contact carrier, the insulator becomes the wire location and insertion aid without any special tools. The wire is just inserted into the cap (no stripping required) and then pressed down to provide a secure "Gas Tight" termination. This configuration simplifies and cost reduces the entire wire termination process for connecting discrete wires to a PCB.

## **APPLICATIONS**

- Connecting discrete wire components to a PCB
- Bringing power and signals onto a PCB
- Daisy chaining PCB's together to create a continuous string
- Reference Product Specification 201-01-140

## **FEATURES AND BENEFITS**

- IDC contact provides a gas-tight connection to the PCB for long term reliability
- Plastic cap retains the contacts in position prior to automatic placement, then acts as the assembly tool to terminate the wires; no special tooling.
- Tested to automotive levels on shock, vibration and temperature cycling for reliability
- Identical contact and footprint pattern to the existing 9176 for full backward compatibility and functionality
- The IDC contact reduces the total applied cost versus solder or crimp processes
- Connectors are available in two configurations for maximum flexibility;
   End and Through Wire

## **ELECTRICAL**

• Current Rating: 10 Amps / Contact

• Voltage Rating: 300 VAC

## **ENVIRONMENTAL**

Operating Temperature:
 -40°C to +125°C


## **MECHANICAL**


Insulator Material: Nylon UL94VOContact Material: Phosphor Bronze

• Plating: Tin over Nickel

Durability 3 Cycles


## **HOW TO ORDER**





7XX










Certification: UL File #E90723







## 18 - 24 AWG 1 WAY IDC CONNECTOR THROUGH WIRE CAPPED IDC














## IOTEC.

- 1 WAY CONNECTOR FOR IDC WIRE TO BOARD CONNECTION. PRE-ASSEMBLED THROUGH WIRE CAP.
- 2. CONTACT/CAP TO MATCH 18-24 AWG STRANDED WIRE INSULATION DIAMETER RANGE AS IN TABLE.
- 3. FLAT FACE ON TOP OF CAP TO AID PICK AND PLACE ASSEMBLY.
- 4. FOR FULL DETAILS REFER TO ELCO SPECIFICATION 201-01-139.
- 5. ASSEMBLY PROCEDURE, REFER TO APPLICATION NOTES 201-01-140.
- 6. GENERAL TOLERANCE ±0.20 UNLESS STATED.
- 7. PACKED IN TAPE AND REEL, QUANTITY PER REEL 600.
- 8. CONNECTOR OUTLINE.
- 9. CONTACT MATERIAL: TIN PLATED COPPER ALLOY.
- 10. INSULATOR MATERIAL: HIGH TEMPERATURE NYLON, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 1.

Code	Accepted Wire Gauge	Α	Wire Insulation	В
701	18 AWG Stranded	0.74	Ø 1.6-2.1	2.1
711	20 AWG Solid and Stranded	0.60	Ø 1.6-2.1	2.1
722	22 AWG Solid and Stranded	0.47	Ø 1.1-1.6	1.6
732	24 AWG Solid and Stranded	0.37	Ø 1.1-1.6	1.6

## 9. 40.0 NOTE 8


SUGGEST PCB LAYOUT








## 18 - 24 AWG 2 WAY IDC CONNECTOR THROUGH WIRE CAPPED IDC





Code	Accepted Wire Gauge	Α	Wire Insulation	В
701	18 AWG Stranded	0.74	Ø 1.6-2.1	2.1
711	20 AWG Solid and Stranded	0.60	Ø 1.6-2.1	2.1
722	22 AWG Solid and Stranded	0.47	Ø 1.1-1.6	1.6
732	24 AWG Solid and Stranded	0.37	Ø 1.1-1.6	1.6

## NOTES:

- 2 WAY CONNECTOR FOR IDC WIRE TO BOARD CONNECTION. PRE-ASSEMBLED THROUGH WIRE CAP.
- 2. CONTACT/CAP TO MATCH 18-24 AWG STRANDED WIRE INSULATION DIAMETER RANGE AS IN TABLE.
- 3. FLAT FACE ON TOP OF CAP TO AID PICK AND PLACE ASSEMBLY.
- 4. FOR FULL DETAILS REFER TO ELCO SPECIFICATION 201-01-139.
- 5. ASSEMBLY PROCEDURE, REFER TO APPLICATION NOTES 201-01-140.
- 6. GENERAL TOLERANCE ±0.20 UNLESS STATED.
- 7. PACKED IN TAPE AND REEL, QUANTITY PER REEL 600.
- 8. CONNECTOR OUTLINE.
- 9. CONTACT MATERIAL: TIN PLATED COPPER ALLOY.
- 10. INSULATOR MATERIAL: HIGH TEMPERATURE NYLON, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 1.

## 8.00 NOTE 8

## SUGGEST PCB LAYOUT


## UNREELED DIRECTION 330mm DIAMETER REEL UNREELED DIRECTION


QUANTITY PER REEL 600





## 18 - 24 AWG 3 WAY IDC CONNECTOR THROUGH WIRE CAPPED IDC





Code	Accepted Wire Gauge	Α	Wire Insulation	В
701	18 AWG Stranded	0.74	Ø 1.6-2.1	2.1
711	20 AWG Solid and Stranded	0.60	Ø 1.6-2.1	2.1
722	22 AWG Solid and Stranded	0.47	Ø 1.1-1.6	1.6
732	24 AWG Solid and Stranded	0.37	Ø 1.1-1.6	1.6

### NOTES:

- 3 WAY CONNECTOR FOR IDC WIRE TO BOARD CONNECTION. PRE-ASSEMBLED THROUGH WIRE CAP.
- 2. CONTACT/CAP TO MATCH 18-24 AWG STRANDED WIRE INSULATION DIAMETER RANGE AS IN TABLE.
- 3. FLAT FACE ON TOP OF CAP TO AID PICK AND PLACE ASSEMBLY.
- 4. FOR FULL DETAILS REFER TO ELCO SPECIFICATION 201-01-139.
- 5. ASSEMBLY PROCEDURE, REFER TO APPLICATION NOTES 201-01-140.
- 6. GENERAL TOLERANCE ±0.20 UNLESS STATED.
- 7. PACKED IN TAPE AND REEL, QUANTITY PER REEL 600.
- 8. CONNECTOR OUTLINE.
- 9. CONTACT MATERIAL: TIN PLATED COPPER ALLOY.
- 10. INSULATOR MATERIAL: HIGH TEMPERATURE NYLON, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 1.

## 12.00 NOTE 8

## SUGGEST PCB LAYOUT

# UNREELED DIRECTION 330mm DIAMETER REEL UNREELED DIRECTION OUANTITY PER REEL 600




## Capped 18-24 AWG: WTB

## 9176-700





## 18 - 24 AWG 1 WAY IDC CONNECTOR WIRE STOP CAPPED IDC
















## 1.


NOTES:

- 1. 1 WAY CONNECTOR FOR IDC WIRE TO BOARD CONNECTION. PRE-ASSEMBLED WIRE SOPT CAP. CODE REFER TO PAGE 1.
- 2. CONTACT/CAP TO MATCH 18-24 AWG STRANDED WIRE. INSULATION DIAMETER RANGE AS IN TABLE.
- 3. FLAT FACE ON TOP OF CAP TO AID PICK AND PLACE ASSEMBLY.
- 4. FOR FULL DETAILS REFER TO ELCO SPECIFICATION 201-01-139.
- 5. ASSEMBLY PROCEDURE, REFER TO APPLICATION NOTES 201-01-140.
- 6. GENERAL TOLERANCE ±0.20 UNLESS STATED.
- 7. PACKED IN TAPE AND REEL, QUANTITY PER REEL 600.
- 8. CONNECTOR OUTLINE.
- 9. CONTACT MATERIAL: TIN PLATED COPPER ALLOY.
- 10. INSULATOR MATERIAL: HIGH TEMPERATURE NYLON, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 1.
- 11. WIRE STOP CAP PROTECTS END OF WIRE.

### Code Wire В Accepted Wire Gauge Insulation 18 AWG Stranded 0.74 Ø 1.6-2.1 2.1 711 20 AWG Solid and Stranded 0.60 Ø 1.6-2.1 | 2.1 22 AWG Solid and Stranded 0.47 Ø 1.1-1.6 1.6 24 AWG Solid and Stranded Ø 1.1-1.6

## 


SUGGEST PCB LAYOUT








## 18 - 24 AWG 2 WAY IDC CONNECTOR WIRE STOP CAPPED IDC





Code	Accepted Wire Gauge	Α	Wire Insulation	В
701	18 AWG Stranded	0.74	Ø 1.6-2.1	2.1
711	20 AWG Solid and Stranded	0.60	Ø 1.6-2.1	2.1
722	22 AWG Solid and Stranded	0.47	Ø 1.1-1.6	1.6
732	24 AWG Solid and Stranded	0.37	Ø 1.1-1.6	1.6

## NOTES:

- 1. 2 WAY CONNECTOR FOR IDC WIRE TO BOARD CONNECTION. PRE-ASSEMBLED WIRE SOPT CAP. CODE REFER TO PAGE 1.
- 2. CONTACT/CAP TO MATCH 18-24 AWG STRANDED WIRE. INSULATION DIAMETER RANGE AS IN TABLE.
- 3. FLAT FACE ON TOP OF CAP TO AID PICK AND PLACE ASSEMBLY.
- 4. FOR FULL DETAILS REFER TO ELCO SPECIFICATION 201-01-139.
- 5. ASSEMBLY PROCEDURE, REFER TO APPLICATION NOTES 201-01-140.
- 6. GENERAL TOLERANCE ±0.20 UNLESS STATED.
- 7. PACKED IN TAPE AND REEL, QUANTITY PER REEL 600.
- 8. CONNECTOR OUTLINE.
- 9. CONTACT MATERIAL: TIN PLATED COPPER ALLOY.
- 10. INSULATOR MATERIAL: HIGH TEMPERATURE NYLON, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 1.
- 11. WIRE STOP CAP PROTECTS END OF WIRE.

## SUGGEST PCB LAYOUT

## UNREELED DIRECTION 330mm DIAMETER REEL UNREELED DIRECTION


OUANTITY PER REEL 600


## Capped 18-24 AWG: WTB

## 9176-700



## 18 - 24 AWG 3 WAY IDC CONNECTOR WIRE STOP CAPPED IDC







Code	Accepted Wire Gauge	Α	Wire Insulation	В
701	18 AWG Stranded	0.74	Ø 1.6-2.1	2.1
711	20 AWG Solid and Stranded	0.60	Ø 1.6-2.1	2.1
722	22 AWG Solid and Stranded	0.47	Ø 1.1-1.6	1.6
732	24 AWG Solid and Stranded	0.37	Ø 1.1-1.6	1.6

## NOTES:

- 2 WAY CONNECTOR FOR IDC WIRE TO BOARD CONNECTION.
   PRE-ASSEMBLED WIRE SOPT CAP. CODE REFER TO PAGE 1.
- 2. CONTACT/CAP TO MATCH 18-24 AWG STRANDED WIRE. INSULATION DIAMETER RANGE AS IN TABLE.
- 3. FLAT FACE ON TOP OF CAP TO AID PICK AND PLACE ASSEMBLY.
- 4. FOR FULL DETAILS REFER TO ELCO SPECIFICATION 201-01-139.
- 5. ASSEMBLY PROCEDURE, REFER TO APPLICATION NOTES 201-01-140.
- 6. GENERAL TOLERANCE ±0.20 UNLESS STATED.
- 7. PACKED IN TAPE AND REEL, QUANTITY PER REEL 600.
- 8. CONNECTOR OUTLINE.
- 9. CONTACT MATERIAL: TIN PLATED COPPER ALLOY.
- 10. INSULATOR MATERIAL: HIGH TEMPERATURE NYLON, GLASS FILLED, UL94 V-0. COLOR REFER TO PAGE 1.
- 11. WIRE STOP CAP PROTECTS END OF WIRE.











## 18-24 AWG ASSEMBLED CAPPED IDC CONNECTORS



**TYPICAL THROUGH WIRE ASSEMBLY** 



**TYPICAL WIRE STOP ASSEMBLY**