


# ENERGIZER XR92

ECO ADVANCED

AAA



## Industry Standard Dimensions




## Specifications

|                         |                                                                              |
|-------------------------|------------------------------------------------------------------------------|
| <b>Classification:</b>  | Alkaline                                                                     |
| <b>Chemical System:</b> | Zinc-Manganese Dioxide (Zn/MnO <sub>2</sub> )<br>No added mercury or cadmium |
| <b>Designation:</b>     | ANSI-24A, IEC-LR03                                                           |
| <b>Nominal Voltage:</b> | 1.5 volts                                                                    |
| <b>Nominal IR:</b>      | 150 to 300 milliohms (fresh)                                                 |
| <b>Operating Temp:</b>  | -18°C to 55°C (0°F to 130°F)                                                 |
| <b>Typical Weight:</b>  | 11.9 grams (0.4 oz.)                                                         |
| <b>Typical Volume:</b>  | 3.8 cubic centimeters (0.2 cubic inch)                                       |
| <b>Jacket:</b>          | Plastic Label                                                                |
| <b>Shelf Life:</b>      | 12 years at 21°C                                                             |
| <b>Terminal:</b>        | Flat Contact                                                                 |


## Milliamp-Hours Capacity

Continuous discharge to 0.8 volts at 21°C




## Constant Power Performance

Typical Characteristics (21°C)



## Constant Current Performance

Typical Characteristics (21°C)




# ENERGIZER XR92

AAA


## Constant Power Performance

Discharge Characteristics (21°C)




## Constant Current Performance

250 mA Discharge (-20°C / 0°C / 21°C)




## Industry Standard Tests (21°C)


### LIGHTING 5.1 ohm LIF




### REMOTE 24 ohm 15 sec/min 8 hrs/day



### TAPE-GAME-DIGITAL AUDIO 100 mA 1 hr/day



### PHOTOFLASH 600 mA 10 sec/min 1 hr/day



Pack Quantity : 4  
Manufacturers Part Number : E300128100  
Pack Quantity : 8  
Manufacturers Part Number : E300116300  
Pack Quantity : 20  
Manufacturers Part Number : E300488000