



REV.	MODIFICATION.	DATE	DRN
01	Production Release	03/01/08	TC
02	CO2010469	11/11/08	SF

NOTE!
• NOT SUPPLIED WITH CABLE TIES - TO BE ORDERED SEPARATELY
• CAN BE ASSEMBLED WITH CABLE TIE BY SPECIAL ORDER ONLY
• HOUSING AVAILABLE IN UL94 V0 NYLON 6/6 (RMS-19) AND
UL94 V2 HEAT STABILIZED NYLON 6/6 (RMS-47) BY SPECIAL ORDER

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.



ALL DIMENSIONS IN mm [Inch]
GENERAL TOLERANCES ± 0.25 [0.0098]
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ± 0.25 [0.0098]
2 DECIMAL PLACES ± 0.10 [0.0039]
ANGULAR ± 1°

THIRD ANGLE


2	HOUSING	NYLON 6/6 UL94 V2 (RMS-01)	BLACK	0.8 - 3 [0.03 - 0.12]	TO STEEL PANEL: Minimum 25N 0.8 [0.03] Panel Minimum 45N 3 [0.12] Panel	WITE/WIT-30 / 40 / 50 QTE-18 / 30 / 50
1	METAL CLIP	STAINLESS STEEL (RMS-365) GRADE 304 (1.4301)	TYPE '2B' BRIGHT FINISH		TO PLASTIC PANEL: Minimum 150N 2.4 - 3 [0.09 - 0.12]	
ITEM	DESCRIPTION	MATERIAL	COLOUR	PANEL THICKNESS	RETENTION FORCE	CABLE TIES ACCEPTED

MATERIAL: SEE TABLE				COLOR: SEE TABLE	
DESCRIPTION: EDGE CLIP TIE HOLDER				PART No: FTH-31-01	
DRG No: 07-073		NPR No: 2005-205-3		Mass:(g) 1.4	SHEET SIZE A4
DRN TC	DATE 10/01/06	CHKD JC	DATE 31/07/07	SCALE NTS	SHEET No. 1 OF 1