

Evaluation Board for the **AD5686R** 16-Bit, Quad Channel, Voltage Output DAC

FEATURES

Full featured evaluation board for the **AD5686R**
 On-board references
 Various link options
 PC control in conjunction with the Analog Devices, Inc.,
System Demonstration Platform (SDP)

EVALUATION KIT CONTENTS

EVAL-AD5686RSDZ (**AD5686R** evaluation board)

CD includes

- Self installing software that allows users to control the board and exercise all functions of the device
- Electronic version of the **AD5686R** data sheet
- Electronic version of the **EVAL-AD5686RSDZ** user guide

USB cable

GENERAL DESCRIPTION

This user guide details the operation of the evaluation board for the **AD5686R** quad channel, voltage output digital-to-analog converter (DAC).

The **EVAL-AD5686RSDZ** evaluation board is designed to help users quickly prototype new **AD5686R** circuits and reduce design time. The **AD5686R** operates from a single 2.7 V to 5.5 V supply. The **AD5686R** incorporates an internal 2.5 V reference to give an output voltage of 2.5 V or 5 V. The evaluation board also incorporates additional voltage references.

Full data on the **AD5686R** can be found in the data sheet, available from Analog Devices, which should be consulted in conjunction with this user guide when using the evaluation board.

The **EVAL-AD5686RSDZ** interfaces to the USB port of a PC via an SDP board. Software is supplied with the evaluation board to allow the user to program the **AD5686R**. A PMOD™ connection is also available for different microcontrollers.

This evaluation board is compatible with any Analog Devices SDP board, which can be purchased separately. For example, a typical connection between the **EVAL-AD5686RSDZ** and the **EVAL-SDP-CS1Z** board (SDP-S controller board) is shown in Figure 1.

EVAL-AD5686RSDZ CONNECTED TO THE SDP-S BOARD




Figure 1.

TABLE OF CONTENTS

Features	1	Link Options	3
Evaluation Kit Contents.....	1	Evaluation Board Software.....	5
General Description	1	Installing the Software	5
EVAL-AD5686RSDZ Connected to the SDP-S Board	1	Running the Software	5
Revision History	2	Software Operation	6
Evaluation Board Hardware.....	3	Full SPI Command.....	6
Power Supplies	3	Evaluation Board Schematics and Artwork.....	7
LDO Recommendation	3	Ordering Information.....	11
Test Points.....	3	Bill of Materials.....	11
Voltage References.....	3		

REVISION HISTORY

5/15—Revision 0: Initial Version

EVALUATION BOARD HARDWARE

POWER SUPPLIES

The [EVAL-AD5686RSDZ](#) provides an on-board, 3.3 V regulator powered through the USB supply. If a different supply is required or if the board is controlled through the PMOD, an external supply must be provided by the EXTSUP connector. See Table 1 for more details.

Both AGND and DGND inputs are provided on the board. The AGND and DGND planes are connected at one location close to the [AD5686R](#). To avoid ground loop problems, it is recommended that AGND and DGND not be connected elsewhere in the system.

All supplies are decoupled to ground with 10 μ F tantalum and 0.1 μ F ceramic capacitors.

LDO RECOMMENDATION

The [ADP7118](#) low dropout (LDO) linear regulator (maximum $V_{IN} = 20$ V) is recommended to power the V_{DD} rail for maximal performance. A 4.7 Ω resistor in series with the input capacitor of the [ADP7118](#) adds additional rejection at higher frequencies to reduce any power supply ripple artifacts below the noise floor. The [ADP162](#) is recommended for powering the V_{LOGIC} rail.

TEST POINTS

The evaluation board has various test points for debugging and monitoring purposes. These test points are described in Table 4.

VOLTAGE REFERENCES

The [AD5686R](#) provides an internal voltage reference. The evaluation board provides external references with values of 2.5 V and 5 V. Note that the [ADR3450](#) requires the use of an external supply through the EXTSUP connector (see Table 3).

LINK OPTIONS

A number of link options are incorporated in the evaluation board and must be set for the required operating conditions before using the board. The functions of these link options are described in Table 3.

Table 2 lists the positions of the different links controlled by the PC via the USB port. An SDP board operating in single-supply mode is required.

Table 1. Power Supply Connectors

Connector	Label	External Voltage Supplies Description
EXTSUP 1 EXTSUP 2	EXTSUP	External analog power supply from 2.7 V to 5.5 V, V_{DD} . Analog ground.
EXTREF 1 EXTREF 2	EXTREF	External voltage reference, V_{LOGIC} . 3.3 V when the evaluation board is controlled through the SDP board. 1.8 V to 5.5 V when the evaluation board is controlled through an external connector. Analog ground.

Table 2. Link Options Setup for SDP Control (Default)

Link	Option
PWRSEL	3.3 V
REF	Not connected
P1	Not connected

Table 3. Link Functions

Link	Description
PWRSEL	This link selects the DAC analog voltage source. There are three options as follows: The 3.3 V option selects the on-board voltage source from the ADP121 . The USB_SUP option selects the USB supply from Pin 5 of the 120-pin connector of the SDP board. The EXT_SUP option selects an external supply voltage (EXTSUP connector).
REF	This link selects the reference source. There are four options as follows: The not connected option uses the 2.5 V internal reference. The EXT_REF option selects an external reference source (EXTREF connector). The 2.5 V option selects the on-board reference from the REF192 . The 5 V option selects the on-board reference from the ADR3450 . This reference requires an external supply.
P1	The P1 link selects the DAC digital voltage source. There are two options as follows: The connected option shorts V_{DD} and V_{LOGIC} . Use this option only when the SDP board is not connected. The not connected option opens the connection of V_{DD} and V_{LOGIC} . Use this option when using the SDP board.

Table 4. Test Point Descriptions

Test Point	Description
AGND	Analog Ground.
DGND	Digital Ground.
SCLK/A0	Serial Clock Input. Data is clocked into the input shift register on the falling edge of the serial clock input. Data can be transferred at rates of up to 50 MHz. This signal is named SCLK_A0 in Figure 6.
SDO/SDA	Serial Data Output. This output daisy chains a number of AD5686R/AD5685R/AD5684R devices together, or it can be used for readback. The serial data is transferred on the rising edge of SCLK and is valid on the falling edge of the clock. This signal is named SDO_SDA in Figure 6.
SYNCB/SCL	Active Low Control Input. This is the frame synchronization signal for the input data. When SYNCB goes low, data is transferred in on the falling edges of the next 24 clocks. This signal is named SYNCB_SCL in Figure 6.
SDIN/A1	Serial Data Input. This device has a 24-bit input shift register. Data is clocked into the register on the falling edge of the serial clock input. This signal is named SDIN_A1 in Figure 6.
VOUTA to VOUTD	Analog Output Voltage from DAC A to DAC D, Respectively. The output amplifier has rail-to-rail operation.

EVALUATION BOARD SOFTWARE

INSTALLING THE SOFTWARE

The evaluation kit for the [AD5686R](#) includes self installing software on the CD. The software is compatible with Windows® XP (32-bit), Windows Vista, and Windows 7 (32-bit and 64-bit). To ensure that the SDP board is recognized when it connects to the PC, the software must be installed before connecting the SDP board to the USB port of the PC.

To install the software, take the following steps:

1. Start the Windows operating system and insert the CD.
2. The installation software opens automatically. If it does not open automatically, run the **setup.exe** file from the CD.
3. After installation is complete, power up the evaluation board as described in the Power Supplies section.
4. Connect the evaluation board to the SDP board and the SDP board into the PC using the USB cable included in the box.
5. When the software detects the evaluation board, proceed through the dialog boxes that appear to finalize the installation.

RUNNING THE SOFTWARE

To run the program, take the following steps:

1. Connect the evaluation board to the SDP board and connect the USB cable between the SDP board and the PC.
2. Click **Start > All Programs > Analog Devices > AD5686R** to run the software. When the software connects to the evaluation board, the message in Figure 2 displays.




Figure 2. Connection Message

3. If the SDP board is not connected to the USB port when the software is launched, a connectivity error displays (see Figure 3). Connect the evaluation board to the USB port of the PC, wait a few seconds, click **Rescan**, and follow the on-screen instructions.




Figure 3. Connectivity Error

4. Alternatively, you can use the software without an evaluation board. The software runs in simulation mode, displaying expected outputs based on the input data (see Figure 4). Note that a 2.5 V reference voltage is used in simulation mode. The main window of the [AD5686R](#) evaluation software then opens, as shown in Figure 5.




Figure 4. Simulation Mode




Figure 5. AD5686R Evaluation Software Main Window

SOFTWARE OPERATION

The software for the [AD5686R](#) allows the user to program values to the input and DAC registers of each DAC individually or collectively.

Write to Input Register

Click **Write to Input Register** to load the value in the **INPUT VALUE (HEX)** box to the input register of any DACs selected in the **DAC A**, **DAC B**, **DAC C**, and **DAC D** check boxes.

Write to DAC Register

Click **Write to Input and DAC Register** to load the value in the input data control to the DAC register of any DACs selected in the **DAC A**, **DAC B**, **DAC C**, and **DAC D** check boxes. The DAC outputs are automatically updated with the appropriate voltage.

Update DAC Register from Input Register

Click **Update DAC Register from Input Register** to copy the value in a DAC input register to the corresponding DAC register. DAC outputs are automatically updated with the appropriate voltage.

LDAC CONTROL

From the **HARDWARE LDAC PIN** drop-down box, select **LDAC LOW** to bring the LDAC pin low and then select **LDAC HIGH** to return it to high. This action copies the data from the input registers to the DAC registers, updating the outputs accordingly.

GAIN Control

The logic level of the **GAIN** pin is set by the GPIO of the SDP and is controlled by the software. To display the correct voltage, the gain selection must be set to match the level of the **GAIN** pin. Set the gain selection by selecting the $\times 1$ or $\times 2$ option from the **GAIN** drop-down box.

Reference Control

The [AD5686R](#) has an on-chip reference that can be disabled to reduce power consumption. Disable the on-chip reference by selecting **Reference OFF** from the **REFERENCE** drop-down box.

Power-Down Control

Each of the DACs can be powered down individually. Each of the DACs has an associated **POWER-DOWN DAC x** drop-down box that allows the device to operate in normal mode, be powered down with either a 1 k Ω or a 100 k Ω resistor to ground, or be three-state. When a power-down mode is selected, the software sends the appropriate command to the [AD5686R](#) and sets the appropriate channel to the selected power-down mode.

FULL SPI COMMAND

The SPI commands sent to the DAC are displayed in the **Full SPI Command** box. This command in hexadecimal format shows what must be written to the [AD5686R](#) to replicate the function of the evaluation board if a different controller is used.

EVALUATION BOARD SCHEMATICS AND ARTWORK




Figure 6. EVAL-AD5686RSDZ Schematic—Power Supply and Signal Routes

12474-006




Figure 7. EVAL-AD5686RSDZ Schematic—SDP Connector




Figure 8. EVAL-AD5686RSDZ Component Silkscreen




Figure 9. EVAL-AD5686RSDZ Top Side Routing




Figure 10. EVAL-AD5686RSDZ Bottom Side Routing

ORDERING INFORMATION

BILL OF MATERIALS

Table 5.

Qty	Reference Designator	Description	Supplier/Part Number ¹
1	U1	32 kΩ, I ² C serial EEPROM (24LC32)	FEC 1331330
1	U2	150 mA, low quiescent current, CMOS linear regulator	Analog Devices ADP121
1	U3	2.5 V precision micropower, low dropout, low voltage reference	Analog Devices REF192
1	U4	Quad, 16-bit <i>nano</i> DAC+ with 2 ppm/°C on-chip reference and SPI interface	Analog Devices AD5686R
1	U5	Micropower, high accuracy, 5.0 V voltage reference	Analog Devices ADR3450
6	C1, C2, C5, C6, C18, C25	Capacitor, 0.1 μF, 16 V, 0402	Generic
3	C4, C17, C19	Capacitor, 1 μF, 25 V, X5R	Generic
4	C3, C8, C20, C24	Capacitor, 10 μF, 10 V, tantalum	Generic
1	C21	Capacitor, 10 μF, 25 V, X5R	Generic
1	C22	Capacitor, 4.7 μF, 25 V, X5R	Generic
1	C23	Capacitor, 0.1 μF, 25 V, X8R	Generic
1	E1	Ferrite bead, 600 Ω	Generic
1	E2	Ferrite bead, 330 Ω	Generic
2	EXTREF, EXTSUP	2-pin terminal block	Generic
1	P1	2-pin link/jumper	Generic
2	REF, PWRSEL	6-pin link/jumper	Generic
1	R12	Resistor, 1.8 Ω, 5%, 1/10 W, thick film chip	Generic
1	R13	Resistor, 0 Ω, SMD	Generic
4	R4, R8, R14, R16	Resistor, 0 Ω, 5%, 1/16 W, 0603	Generic
2	R2, R3	Resistor, 100 kΩ, 1%, 1/10 W	Generic
1	SDP	120-pin female connector	FEC 1324660 or Digi-Key H1219-ND
2	AGND, DGND	Black test point	Generic
4	SCLK/A0, SDIN/A1, SDO/SDA, SYNCB/SCL	White test point	Generic
4	VOUTA to VOUTD	Red test point	Generic
19	PMOD, C11, C12, C15, C16, R1, R5 to R7, R9 to R11, R15, R17, R20, VOUT_A to VOUT_D	Do not insert/populate (DNI)	Not inserted

¹ Generic indicates that any part with the specified value, size, and rating can be used.

NOTES

**ESD Caution**

ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

Legal Terms and Conditions

By using the evaluation board discussed herein (together with any tools, components documentation or support materials, the "Evaluation Board"), you are agreeing to be bound by the terms and conditions set forth below ("Agreement") unless you have purchased the Evaluation Board, in which case the Analog Devices Standard Terms and Conditions of Sale shall govern. Do not use the Evaluation Board until you have read and agreed to the Agreement. Your use of the Evaluation Board shall signify your acceptance of the Agreement. This Agreement is made by and between you ("Customer") and Analog Devices, Inc. ("ADI"), with its principal place of business at One Technology Way, Norwood, MA 02062, USA. Subject to the terms and conditions of the Agreement, ADI hereby grants to Customer a free, limited, personal, temporary, non-exclusive, non-sublicensable, non-transferable license to use the Evaluation Board FOR EVALUATION PURPOSES ONLY. Customer understands and agrees that the Evaluation Board is provided for the sole and exclusive purpose referenced above, and agrees not to use the Evaluation Board for any other purpose. Furthermore, the license granted is expressly made subject to the following additional limitations: Customer shall not (i) rent, lease, display, sell, transfer, assign, sublicense, or distribute the Evaluation Board; and (ii) permit any Third Party to access the Evaluation Board. As used herein, the term "Third Party" includes any entity other than ADI, Customer, their employees, affiliates and in-house consultants. The Evaluation Board is NOT sold to Customer; all rights not expressly granted herein, including ownership of the Evaluation Board, are reserved by ADI. CONFIDENTIALITY. This Agreement and the Evaluation Board shall all be considered the confidential and proprietary information of ADI. Customer may not disclose or transfer any portion of the Evaluation Board to any other party for any reason. Upon discontinuation of use of the Evaluation Board or termination of this Agreement, Customer agrees to promptly return the Evaluation Board to ADI. ADDITIONAL RESTRICTIONS. Customer may not disassemble, decompile or reverse engineer chips on the Evaluation Board. Customer shall inform ADI of any occurred damages or any modifications or alterations it makes to the Evaluation Board, including but not limited to soldering or any other activity that affects the material content of the Evaluation Board. Modifications to the Evaluation Board must comply with applicable law, including but not limited to the RoHS Directive. TERMINATION. ADI may terminate this Agreement at any time upon giving written notice to Customer. Customer agrees to return to ADI the Evaluation Board at that time. LIMITATION OF LIABILITY. THE EVALUATION BOARD PROVIDED HEREUNDER IS PROVIDED "AS IS" AND ADI MAKES NO WARRANTIES OR REPRESENTATIONS OF ANY KIND WITH RESPECT TO IT. ADI SPECIFICALLY DISCLAIMS ANY REPRESENTATIONS, ENDORSEMENTS, GUARANTEES, OR WARRANTIES, EXPRESS OR IMPLIED, RELATED TO THE EVALUATION BOARD INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, TITLE, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS. IN NO EVENT WILL ADI AND ITS LICENSORS BE LIABLE FOR ANY INCIDENTAL, SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES RESULTING FROM CUSTOMER'S POSSESSION OR USE OF THE EVALUATION BOARD, INCLUDING BUT NOT LIMITED TO LOST PROFITS, DELAY COSTS, LABOR COSTS OR LOSS OF GOODWILL. ADI'S TOTAL LIABILITY FROM ANY AND ALL CAUSES SHALL BE LIMITED TO THE AMOUNT OF ONE HUNDRED US DOLLARS (\$100.00). EXPORT. Customer agrees that it will not directly or indirectly export the Evaluation Board to another country, and that it will comply with all applicable United States federal laws and regulations relating to exports. GOVERNING LAW. This Agreement shall be governed by and construed in accordance with the substantive laws of the Commonwealth of Massachusetts (excluding conflict of law rules). Any legal action regarding this Agreement will be heard in the state or federal courts having jurisdiction in Suffolk County, Massachusetts, and Customer hereby submits to the personal jurisdiction and venue of such courts. The United Nations Convention on Contracts for the International Sale of Goods shall not apply to this Agreement and is expressly disclaimed.