FG300 SERIES

FUNKTIONSGENERATOR

FUNCTION GENERATOR

GEBRAUCHSANWEISUNG

OPERATING INSTRUCTIONS

digimess®



((

Bestell-Nr. Order No.

FG303 HUC62-01 FG308 HUC62-02

Subject to alterations, errors excepted

©Convright 2012

FG300 Series Function Generator Operating Instructions

1.0 A Mains Connection

The design of the unit meets the requirements of safety class I according to EN 61010-1, i.e. all metal parts accessible from outside and exposed to contact are connected with the protective conductor of the supply network.

Power is supplied via a mains cable with earthing contact

1.1 Installing the function generator

The function generator should not be operated close to equipment that develops heat. To protect the unit from thermal overload the air vents must not be covered and a free space of about 10 cm should be ensured.

1.2 Switching on

The function generator is switched on using the power switch at the front. The power switch separates the unit completely from the primary side of the transformer.

1.3 EMC

The function generator is interference-free according to EN 50081-1 and EN 50081-2. In order to fulfil the limit values in line with present standards, it is absolutely necessary that only cables which are in perfect condition be connected to the unit.

1.4 Inspection and Maintenance

If service is needed, due attention should be paid to the regulations according to VDE 0701. The function generator should only be repaired by trained personnel.

1.5 Warranty

The perfect working order of the function generator is guaranteed for 12 months as from delivery.

There is no warranty for faults arising from improper operation or from changes made to the function generator or from inappropriate application.

If a fault occurs please contact or send your function generator to:

| Agents detail | ls: | | |
|---------------|-----|--|--|
| | | | |
| | | | |
| | | | |
| | | | |

The function generator should be sent in appropriate packing - if possible in the original packing. Please enclose a detailed fault report (functions working incorrectly, deviating specifications and so on) including unit type and serial number.

Would you also kindly verify warranty cases by enclosing your supply delivery note. Any repairs carried out without reference to a valid warranty will initially be at the owner's expense.

Should the warranty have expired, we will, of course, be glad to repair your function generator as per our General Terms Of Assembly And Service.

1.6 Description

The *digimess*[®] FG300 series are general purpose Direct Digital Synthesis (DDS) function generators with frequencies to 3MHz (FG303) and 8MHz (FG308). Frequency setting is by keypad entry or rotary control and the combination of soft touch buttons and rotary controls for the remaining features result in a modern and easy to use instrument. These versatile generators have a 6 digit frequency display for internal or external signals and a 4 digit output amplitude display. The comprehensive specification also includes an output on/off switch and a variable TTL/CMOS amplitude control. Further features include LED indicators for frequency, amplitude and attenuation ranges as well as the selected waveform shape.

2 Technical Data

2.1 General Data

Nominal temperature: $+23 \,^{\circ}\text{C} \pm 1 \,^{\circ}\text{C}$ Operating temperature: $0 \text{ to } +40 \,^{\circ}\text{C}$ Relative humidity: Upto 75 % Atmospheric pressure: 70 to 106 kPa

Operating position: horizontal or inclined by $\pm 15^{\circ}$

Operating voltage: sinusoidal alternating voltage (distortion factor < 5 %)

220 V (+ 10 %)

Frequency: $50Hz (\pm 5 \%)$

Safety class: 1, according to EN 61010 Part 1

Radio interference suppression: EN 55011 Class B

4

2.2 Specifications

| Specification | | | | |
|---------------------------|--|----------------------------------|--|--|
| | | TTL amplitude | ≥3Vpp | |
| FREQUENCY | | TTL fan out | 20 TTL loads | |
| Frequency range (FG303) | Sine 0.1Hz to 3MHz Square 0.1Hz to 2MHz Triangle 0.1Hz to 1MHz | CMOS amplitude | 3.5 to 13.5Vpp | |
| Frequency range (FG308) | Sine 0.1Hz to 8MHz Square 0.1Hz to 2MHz Triangle 0.1Hz to 1MHz | DISPLAYS Frequency readout | 6 digit LED | |
| Resolution | 100mHz | External frequency range | 10Hz to 60MHz | |
| Stability | ±1 x 10 -6 | External voltage range | 0.2V to 20V -4 | |
| Error | ±5 x 10 | Error | ±1 x 10 | |
| Accuracy | ±50ppm | Voltage readout | 4 digit LED | |
| ОИТРИТ | | GENERAL | | |
| Waveforms | Sine, Square, Triangle, TTL/CMOS | Input voltage | 220Vac ±10% 50Hz ±5% | |
| Output level | 20mV to 20Vpp (no load) | Weight | Approx 1.5kg | |
| Attenuation | 0dB, -40dB | Size W x H x D | 265(W) x110(H) x340(D) mm | |
| Output impedance | 50Ω ±10% | Temperature | Operating 0°C to 40°C | |
| DC offset | ±10V (no load) | | Storage –20°C to 70°C | |
| Duty cycle | 20% to 80% | Humidity | Up to 75% | |
| WAVEFORMS | | ORDERING INFORMATION | | |
| Sine distortion | <0.6% 1kHz | HUC62-01 FG303 HUC62-02 FG308 | 3MHz function generator 8MHz function generator | |
| Triangle linearity | ≥98% 100mHz to 100kHz ≥95% 100kHz to 1MHz | Accessories supplied | Operators manual BNC test lead | |
| Square rise and fall time | <60ns | | Mains lead | |

:

3.0 Operating instructions

3.1 Mains input

The mains input connector is located on the rear of the unit. Before connecting to the mains supply the user should verfy that the unit is set to the correct voltage for the country of use.

3.2 Mains input fuse

The mains fuse is located on the rear of the unit. The fuse should be F1A 250V for 110Vac and F500mA 250V for 220Vac.

3.3 Power on/off

The mains power to the unit is switched on and off using the POWER on/off pushbutton. After switching the power on the unit performs an internal self test. After successful completon of the self test the unit is ready for use. Note: controls should not be adjusted during the self test as errors may occur and the unit would require resetting by turning off and then on again.

3.4 Frequency setting

Press SHIFT +5 (V/F) to switch between frequency and amplitude display.

Set frequency

The frequency is set using the numeric keypad. Enter the desired frequency on the keypad followed by SHIFT and either +8 (MHz), +9 (kHz) or +0 (Hz). If the frequency exceeds the maximum setting an Error message is displayed.

Edit frequency

Push the Frequency control knob to move the cursor to the correct position. Turn the Frequency control knob to change the frequency setting. If the frequency exceeds the maximum setting an Error message is displayed.

3.5 Amplitude setting

Press SHIFT +5 (V/F) to switch between frequency and amplitude display. The amplitude of the 50 ohm output is adjusted by using the AMPL control and the set amplitude is then shown on the LED display. The attenuation of the output amplitude is selected using the SHIFT and +4 (0dB) or SHIFT +3 (40dB) pushbuttons.

3.6 Offset

The output offset level can be adjusted by usng the OFFSET control. In the off position the offset is zero.

3.7 Symmetry

The symmetry (duty cycle) of the output waveform can be adjusted using the DUTY control. In the off position the symmetry (duty cycle) is 50%

3.8 50 ohm output

The 50 ohm output socket provides the main output of the unit from a 50 ohm source impedance.

(

3.9 TTL/CMOS output

Press SHIFT +TTL/CMOS to acivate the TTL/CMOS output. This output socket provides a TTL or CMOS level square wave signal adjustable between 3V and 13.5V using the TTL/CMOS control. In the off position the output is 5V.

3.10 Frequency counter external input

The unit can be used as a frequency counter for external signals by pressing SHIFT +7 (COUNTER) pushbutton. The counters frequency range is 10Hz to 60MHz with an input signal to the connector on the rear panel between 0.2V and 20V.

3.11 Output ON

The output is switched on using the OUTPUT ON pushbutton.

3.12 Waveform select

The output waveform can be set to sinewave, trangle wave or square wave by using the WAVE pushbutton.

3.13 Power output

The power output is not fitted to these models and the PO push button has therefore no effect.

,



Konformitatserklarung Declaration of Conformity / Declaration de Conformite



Der Hersteller/importeur The manufacturer/importer

Le producteur/importateur

Anschrift/Address/Adresse Stenson House

Stenson Derby DE73 1HL ENGLAND

erklart hiermit eigenverantwortlich, dass das

Produkt:

hereby declares that the product :

declare, que le produit :

Bezeichnung/Name/Description Funktionsgenerator

Function generator Generateur de fonctions

Digimess Instruments Ltd

Type/Model/Type FG303, FG308

Bestell-Nr/Order No/No de ref HUC62-01, HUC62-02

Folgenden Normen entspricht: EN61010-1 (1994)

is in accordance with the following DIN EN 50081-1 (1993) DIN EN 50081-2 (1994)

specifications: EN50082

correspond aux normes suivantes : EN 55011 (1991) Class B

EN 55022 (1987) Class B

IEC 801-2 (1991)/prEN 55024-2 (1992) 2kV IEC 801-4 (1988)/prEN 55024-4 (1993) 1kV Burst

IEC 801-3 (1984) 3V/m; 0,15-150MHz

Das Produkt erfullt somit die Forderungen

folgender EG-Richtlinien:

Therefore the product fulfills the demands of

the following EC-Directives:

Le produit satisfait ainsi aux conditions des

directives suivantes de la CE:

EN61000-3-3 2002/95/EC RoHS 2002/96/EC WEEE

EN61000-3-2

73/23/EWG Richtlinie betreffend elektrische Betriebsmittel zur

Verwendung innerhalb bestimmter Spannungsgrenzen Directive relating to electrical equipment designed for

use within certain voltage limits

Directive relatives au materiel electrique destine a etre

employe dans certaines limites de tension

89/336/EWG

Derby, 1.6.2012

Richtlinie uber die elektromagnetische Vertraglichkeit Directive relating to electromagnetic compatibility Directive relatives a la compatibilitie electromagnetique

A Smith

A.P. Smith

Leiter Qualitatsmanagement

Quality Manager/Directeur Controle de Qualite

idilagon/Biroctodi Controlo