


ENERGIZER 386/301

SILVER OXIDE



Industry Standard Dimensions




DESIGNED FOR USE ON CONTINUOUS LOW DRAIN  
HIGH PULSE ON DEMAND

Specifications

|                           |  |
|---------------------------|--|
| <b>Chemical System:</b>   | Silver Oxide (Zn/Ag <sub>2</sub> O)      |
| <b>Designation:</b>       | ANSI/NEDA-1133SO/1132SO, IEC-SR43        |
| <b>Nominal Voltage:</b>   | 1.55 Volts                               |
| <b>Typical Capacity:</b>  | 127 mAh* (to 1.2 volts)                  |
| <b>Capacity Test:</b>     | 6.5K ohm continuous drain at 21°C        |
| <b>Typical Weight:</b>    | 1.7 grams (0.06 oz.)                     |
| <b>Typical Volume:</b>    | 0.44 cubic centimeters (0.27 cubic inch) |
| <b>Impedance (40 Hz):</b> | 5 to 15 ohms                             |

\* Varies according to the applied load, temperature, and cutoff voltage.


Cross Section



Typical Discharge Characteristics

Typical Performance at 21°C (70°F)

Schedule: Continuous  
Typical Drain @1.52V:  
0.234 milliamperes  
Load: 6.5K ohm




| Schedule   | Typical Drains at 1.52V (milliamperes) | Load (ohm) | Cutoff 1.2V (hours) |
|------------|--|------------|---------------------|
| Continuous | 0.234                                  | 6.5K       | 542                 |


Temperature Characteristics

Typical Performance at Low Discharge Rates

Service Effects



Storage Effects



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.  
© Energizer Holdings, Inc. - Contents herein do not constitute a warranty.