

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0039000038**  
**Status:** **Active**  
**Overview:** Mini-Fit Jr.™ Power Connectors  
**Description:** Mini-Fit® Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 18-24 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-5556-001 (PDF)</a>
<a href="#">Product Specification PS-5556-001 (PDF)</a>	<a href="#">Test Summary TS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-5556-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<u>5556</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Mini-Fit Jr.™ Power Connectors</u>
Packaging Alternative	<u>39-00-0039 (Loose)</u>
Product Name	Mini-Fit®
UPC	800753585010

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.130/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

Old Part Number	5556T
-----------------	-------

**Reference - Drawing Numbers**

Packaging Specification	PK-5556-001
Product Specification	PS-5556-001, PS-5556-002, RPS-30067-001, RPS-30067-002, RPS-42474-001, RPS-51045-001, RPS-5557-008, RPS-5557-024, RPS-5557-031, RPS-5557-036, RPS-5557-037, RPS-5557-045, RPS-5557-046, RPS-5566-002
Sales Drawing	SD-5556****
Test Summary	TS-5556-002



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

No -ED/39/2015 (15 June 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Compliant

**Search Parts in this Series**

5556 Series

**Mates With**

5558 Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, 5566 , 5569

**Use With**

5557 Mini-Fit Jr.™ Receptacle Housing, 30067 Mini-Fit® TPA, 42474 Mini-Fit® BMI Panel Mount, 5559 Mini-Fit Jr.™ Plug Housing, Dual Row

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

FineAdjust™ Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	<u>0639024800</u>
T2 Terminator™ for insulation OD 2.50-2.95mm - 18-24 AWG	<u>0639102600</u>
T2 Terminator™ for insulation OD 2.50-2.95mm optimized for 18 AWG only	<u>0639124800</u>
T2 Terminator™ for insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639124900</u>
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<u>0638190900</u>
T2 Terminator™ for insulation OD 1.65 – 2.05mm – 18 – 24 AWG	<u>0639102900</u>
T2 Terminator™ for insulation OD 1.40-1.70mm - 18-24 AWG	<u>0639123900</u>
Extraction Tool	<u>0011030044</u>
T2 Terminator™ for insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639115600</u>
FineAdjust™ Applicator for Insulation OD 2.50-2.95mm, 18-24 AWG Wire	<u>0639002600</u>
FineAdjust™ Applicator for Insulation OD 1.65-2.05mm, 18-24 AWG Wire	<u>0639002900</u>
FineAdjust™ Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639015600</u>
FineAdjust™ Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG	<u>0639023900</u>
FineAdjust™ Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639024900</u>

**Japan**

**Description**

**Product #**

Side-Feed Applicator 0570223200  
For Full-Auto  
Machine  
Hand Extraction Tool 0570316000  
Applicator for M21 1A 0570223000  
Bench Press, 18-24  
AWG Wire

This document was generated on 11/23/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**