

Quant 3D


BUILD YOUR IMAGINATION™



“The most approachable model we’ve reviewed, and we’d recommend it to anyone.”

Make:

“A clear winner and easy to use, with feature-rich software and impressive print quality.”



Q 200

In financial circles, the word “quant” is short for quantitative analysis. This is the process of interpreting volumes of quantitative data into meaningful information. Our printers literally translate volumes of engineering data into physical 3D objects. Hence, our brand name Quant 3D.

Whether you are an engineer, an educator, a manufacturer, an inventor, or a hobbyist, unleash your creativity and turn your ideas and designs into professional 3D models, all at the touch of a button!

- Award winning 3D printer
- Best in class auto-level platform
- High quality ABS / PLA
- Easy to use interface
- Top rated magazine reviews

Quant 3D

Q200 FEATURES

- Printing resolution: 150, 200, 250, 300, 350, 400 microns
- Heated platform
- Intuitive user software
- Compact size that fits on any workbench or desk
- Automatic platform leveling calibration
- Automatic platform height calibration
- Plug and play
- Outstanding print quality
- Comes with one spool of premium ABS plastic (white)
- Other ABS filament colors are also available


INCLUDED

- 180W power supply and USB cable
- Easy to use 3D Software
- 700g spool of ABS plastic
- Perforated build platform
- Quick Start Guide
- 12 month warranty
- Tool Kit:
Precision tweezers, support material removal pliers, nozzle wrench, part-lifter, leather work gloves, filament guide lube, spool holder, small parts/tool bag



TECHNICAL SPECIFICATIONS

| | |
|------------------------|--|
| Build Volume (HxWxD) | 5.3 x 5.5 x 5.5 in, 135 x 140 x 140 mm |
| Finest Layer Thickness | 0.15mm |
| Printer Size (HxWxD) | 14 x 9.5 x 10.5 in, 350 x 245 x 260 mm |
| Printer Weight | 5kg / 11lb |
| Power Requirement | 100-240V AC, 50-60Hz, 180W |
| Input File Format | STL |
| OS Supported | Windows XP / Vista / 7 / 8, Mac OS X |



Quant 3D