

ENERGIZER XR91

ECO ADVANCED


AA



Specifications


Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	ANSI-15A, IEC-LR6
Nominal Voltage:	1.5 volts
Nominal IR:	150 to 300 milliohms (fresh)
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Typical Weight:	24.0 grams (0.8 oz.)
Typical Volume:	8.1 cubic centimeters (0.5 cubic inch)
Jacket:	Plastic Label
Shelf Life:	12 years at 21°C
Terminal:	Flat Contact

Industry Standard Dimensions




Milliamp-Hours Capacity

Continuous discharge to 0.8 volts at 21°C




Constant Power Performance

Typical Characteristics (21°C)



Constant Current Performance

Typical Characteristics (21°C)




ENERGIZER XR91




Constant Power Performance

Discharge Characteristics (21°C)







Constant Current Performance

250 mA Discharge (-20°C / 0°C / 21°C)



Industry Standard Tests (21°C)



- Pack Quantity : 4
- Manufacturers Part Number : E300130700
- Pack Quantity : 8
- Manufacturers Part Number : E300116500
- Pack Quantity : 20
- Manufacturers Part Number : E300487800