


(LR14)

C



### Industry Standard Dimensions




### Specifications


|                         |                                                                              |
|-------------------------|------------------------------------------------------------------------------|
| <b>Classification:</b>  | Alkaline                                                                     |
| <b>Chemical System:</b> | Zinc-Manganese Dioxide (Zn/MnO <sub>2</sub> )<br>No added mercury or cadmium |
| <b>Designation:</b>     | IEC-LR14                                                                     |
| <b>Nominal Voltage:</b> | 1.5 volts                                                                    |
| <b>Nominal IR:</b>      | 150 to 300 milliohms (fresh)                                                 |
| <b>Operating Temp:</b>  | -18°C to 55°C                                                                |
| <b>Typical Weight:</b>  | 66.0 grams                                                                   |
| <b>Typical Volume:</b>  | 27.0 cubic centimeters                                                       |
| <b>Jacket:</b>          | Plastic Label                                                                |
| <b>Shelf Life:</b>      | 7 years at 21°C                                                              |
| <b>Terminal:</b>        | Flat Contact                                                                 |

### Milliamp-Hours Capacity


Continuous discharge to 0.8 volts at 21°C



### Industry Standard Testing (21°C):



### Battery Selection Indicator



Pack Quantity : 2  
Manufacturers Part Number : E300129900