

Defence Standard 61-12 Part 4 - 7-1-C Screened Multicore Cable

pro-POWER

RoHS
Compliant



Specifications:

Conductor Material	: Tinned Copper
Conductor Area CSA	: 0.055mm ²
Construction	: T0.1± 0.008×7
Stranded Dia.(mm)	: 0.3
Insulation Material	: PVC
Insulation Colours	: See Insulation Colours Table
Insulation Thickness	: 0.2
Insulation Dia.(+/-0.05mm)	: 0.7
Braid Shield	: Tinned Copper
Nylon Rip Cord	: 150D
Jacket Material	: PVC
Jacket Colour	: Black
Jacket Thickness (mm)	: 0.35

Electrical Characteristics:

Max.Conductor DC Resistance at 20°C (Ω/Km)	: <338.6
20°C Insulation Resistance (MΩ/Km)	: >200
Working Temperature Range	: -30°C to +70°C
Rated Max. Temperature(°C)	: 80
Rated Voltage(V)	: 250

Insulation Colours table

Core Number	Colour	Core Number	Colour
1	Red	14	Green/Red
2	Blue	15	Yellow/Red
3	Green	16	White/Red
4	Yellow	17	Red/Black
5	White	18	Red/Brown
6	Black	19	Yellow/Blue
7	Brown	20	White/Blue
8	Violet	21	Blue/Black
9	Orange	22	Orange/Blue
10	Pink	23	Green/Blue
11	Turquoise	24	Grey/Blue
12	Grey	25	Yellow/Green
13	Red/Blue		

Defence Standard 61-12 Part 4 - 7-1-C Screened Multicore Cable



Part Number Table

Description	Core No.	Jacket Diameter (mm)	Braiding	Filler	Reel Length (m)	Part Number
Cable, Screen, DEF 7-1-2C	2	2.8	T0.1×16×4		25	PP000291
					100	PP000292
Cable, Screen, DEF 7-1-3C	3	3		-	25	PP000293
					100	PP000294
Cable, Screen, DEF 7-1-4C	4	3.2	T0.1×16×5		25	PP000295
					100	PP000296
Cable, Screen, DEF 7-1-6C	6	3.6	T0.1×16×6	0.7PVC Strip	25	PP000297
					100	PP000298
Cable, Screen, DEF 7-1-9C	9	4.2	T0.1×16×8	1.3 PVC Strip	25	PP000299
					100	PP000300
Cable, Screen, DEF 7-1-12C	12	4.4		-	25	PP000301
					100	PP000302
Cable, Screen, DEF 7-1-15C	15	5.2	T0.15×16×6		25	PP000303
					100	PP000304
Cable, Screen, DEF 7-1-25C	25	6.3	T0.15×16×8		25	PP000305
					100	PP000306

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.