

PRODUCT

5CO Carbon Monoxide Alarm



DESCRIPTION

Compact and lightweight battery-powered CO alarm provides essential protection against the dangers of deadly carbon monoxide and provides continuous monitoring of CO levels.

KEY FEATURES

- **Continuous monitoring** of carbon monoxide
- **Multi-function green and red LEDs** to indicate power and alarm status
- **End-of-life alarm** alerts user to replace alarm after a minimum of 7 years' protection
- **Test/Reset button** to allow regular testing of alarm function
- **Battery operation** – 3 x AA alkaline batteries supplied as standard

WHERE TO USE

This small, easy-to-use alarm is ideal for use in all living areas and can be installed on a wall or ceiling or used freestanding on a table or shelf.

GENERAL FEATURES

Model	5CO
Power Supply	3 x AA batteries (as supplied)
Temperature Range	0°C to 40°C
Humidity Range	Up to 90% relative humidity (RH) non-condensing
Storage and Transport	-20°C to +60°C and 5–95% relative humidity (RH) non-condensing
Alarm Dimensions	126 x 72 x 35mm
Alarm Weight	115g
Warranty	7 years
Approvals	BSI certified to EN50291-1:2010

CE tested and certified



EN50291-1: 2010
Licence no. KM98848

PRODUCT

i9040
**Compact
Smoke Alarm**

DESCRIPTION

Compact (4-inch, 10cm), battery-powered smoke alarm for use where space is limited – it uses an ionisation sensor to detect fast-flaming fires that can burn combustible materials quickly and without warning.

KEY FEATURES

- **Combined Test/Hush™ button** allows regular testing of alarm function and can be used to temporarily silence nuisance alarms
- **Battery operation** – 9V battery supplied as standard

WHERE TO USE

This small, easy-to-install battery-powered unit is ideal for use anywhere in the home and provides effective additional protection when used alongside other smoke alarms.

GENERAL FEATURES

Model	i9040
Power Supply	9V battery supplied as standard
Temperature Range	0°C to + 40°C
Humidity Range	Up to 90% Relative Humidity (RH) non-condensing
Storage and Transport	-20°C to +60°C and 5–95% relative humidity (RH) non-condensing
Alarm Dimensions	98 x 98 x 35mm
Alarm Weight	160g
Warranty	3 years
Approvals	LPCB certified to BS EN14604:2005

CE tested and certified

EN14604: 2005
LPCB Ref No 904a/06



0832-CPD-1427
10
EN14604:2005