

SIMATIC S7-1200, ANALOG OUTPUT SB 1232, 1 AO, +/- 10VDC (12 BIT RES.) OR 0 - 20 MA (11 BIT RES)



Input current	
from backplane bus 5 V DC, typ.	15 mA
Output voltage	
Power supply to the transmitters	
• Supply current, max.	25 mA
Power loss	
Power loss, typ.	1.5 W
Analog inputs	
Number of analog inputs	0
Analog outputs	
Number of analog outputs	1
Cycle time (all channels) max.	Voltage: 300 $\mu$ S (R), 750 $\mu$ S (1 $\mu$ F) Current: 600 ms (1 mH); 2 ms (10 mH)
Output ranges, voltage	
• -10 V to +10 V	Yes
Output ranges, current	
• 0 to 20 mA	Yes

<b>Load impedance (in rated range of output)</b>	
• with voltage outputs, min.	1 000 Ω
• with current outputs, max.	600 Ω
<b>Cable length</b>	
• shielded, max.	10 m; shielded, twisted pair
<b>Analog value generation</b>	
Measurement principle	Differential
<b>Integration and conversion time/resolution per channel</b>	
• Resolution (incl. overrange)	V/12 bit, I/11 bit
<b>Smoothing of measured values</b>	
• parameterizable	Yes
<b>Errors/accuracies</b>	
Temperature error (relative to output range), (+/-)	25 °C ±0.5%, to 55 °C ±1%
<b>Interrupts/diagnostics/status information</b>	
Alarms	Yes
Diagnostic functions	Yes
<b>Diagnostics indication LED</b>	
• for status of the outputs	Yes
<b>Degree and class of protection</b>	
Degree of protection acc. to EN 60529	
• IP20	Yes
<b>Standards, approvals, certificates</b>	
CE mark	Yes
CSA approval	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
<b>Ambient conditions</b>	
<b>Free fall</b>	
• Fall height, max.	0.3 m; five times, in dispatch package
<b>Ambient temperature during operation</b>	
• permissible temperature range	0 °C to 55 °C horizontal installation, 0 °C to 45 °C vertical installation
• min.	0 °C
• max.	55 °C
<b>Ambient temperature during storage/transportation</b>	
• min.	-40 °C
• max.	70 °C
<b>Air pressure acc. to IEC 60068-2-13</b>	
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa

<b>Relative humidity</b>	
• permissible range (without condensation) at 25 °C	95 %
<b>Extended ambient conditions</b>	
<b>Pollutant concentrations</b>	
— SO2 at RH < 60% without condensation	SO2: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free
<b>Mechanics/material</b>	
<b>Enclosure material (front)</b>	
• Plastic	Yes
<b>Dimensions</b>	
Width	38 mm
Height	62 mm
Depth	21 mm
<b>Weights</b>	
Weight, approx.	40 g
<b>last modified:</b>	22.01.2016