

111-00698



Article Number: 111-00698

High Temp Cable Tie, 5.9" Long, 30lb Tensile Strength, ETFE, Blue, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 111-00698

Type T30R

Color Blue (BU)

- Features and Benefits**
- ETFE cable ties provide excellent resistance to chemicals, radiation, high temperatures and UV exposure.
 - Inside serrations allows for strong hold on cables and wire bundles.
 - Head design provides high tensile strength with very low insertion force.
 - Bent tail ensures a quick and simple installation.

Product Description HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description High Temp Cable Tie, 5.9" Long, 30lb Tensile Strength, ETFE, Blue, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 30.0 lbs

Minimum Tensile Strength (Metric) 133.3 N

Length L (Imperial) 5.9 "

Length L (Metric) 150 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.14 "

Width W (Metric) 3.5 mm

Bundle Diameter Min. (Imperial) 0.12 "

Bundle Diameter Min. (Metric) 3.0 mm

Bundle Diameter Max. (Imperial) 1.4 "

Bundle Diameter Max. (Metric) 36 mm

Thickness T (Imperial) 0.05 "

Cable Tie Head Length (Imperial) 0.22 "

Cable Tie Head Width (Imperial) 0.24 "

Thickness T (Metric) 1.2

Logistics and Packaging

Quantity Per bag
Package Quantity (Metric) 100 Pieces
Carton Quantity 20000
Weight (Metric) 3.67 kg

Material and Specifications

Material Ethylenterafluoroethylene - (E/TFE)
Material Shortcut E/TFE
Flammability UL94 V0
Operating Temperature -112°F to +338°F (-80°C to +170°C)
ROHS Compliant Yes
Certification/Specification Det Norske Veritas
UL Listed (US and Canada) No
UL Recognized (US and Canada) Yes