

# Waterproof Case

---



## Features:

- Waterproof and dustproof IP67 certified
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins, corrosion free
- Cubed foams in the bottom and convoluted foams in the lid available as standard
- Screen printing space and rectangular resin label space on the lid

## Specifications:

Body and handle	: Polypropylene Copolymer
Latches	: Nylon
Pins	: Nylon +30% Fiberglass
O-ring	: Polymer
Colours	: Black and Red
External Dimensions	: 336mm × 300mm × (H)148mm (13.93" × 11.81" × (H)5.83")
Internal Dimensions	: 300mm × 225mm × (H)132mm (11.81" × 8.86" × (H)5.2")
Lid-Bottom Depth	: 33mm +99mm (1.3" +3.90")
Weight Without Foam	: 1,620g
Weight With Foam	: 1,760g
Moulding	: Injection Molded
Range Temperature	: -30°C to +90°C (-22°F to +194°F)
Features	: IP67
Customization	: Personalized Nameplate/Resin Label
Accessories	: Cubed Foams

## Part Number Table

Description	Part Number
Waterproof Case	MAX300 S.079