

Power PCB Relay RZL

- 1 pole 12/16 A, 1 form C (CO) or 1 form A (NO) contact
- DC coil 530 mW
- 5kV/10mm coil-contact, reinforced insulation
- Ambient temperature 70°C (special applications 85°C)

Typical applications Household appliances, boiler control, timers, garage door control





Approvals in processVDE Cert. No. 40023970, UL E214025, CQC 14001114367, CQC 14002113865

Technical data of approved types on request

Contact Data	12A	16A			
Contact arrangement 1	form C (CO)	or 1 form A (NO)			
Rated voltage	250VAC				
Max. switching voltage	400	VAC			
Rated current	12A	16A			
Limiting making current (form A contact)					
max. 4s, duty factor 10%	3	0A			
Breaking capacity max.	3000VA	4000VA			
Contact material	AgNi	90/10			
Contact style	single	contact			
Frequency of operation, with/without loa	id 360/72	2000h ⁻¹			
Operate/release time max.	8/6	Sms			
Bounce time max., form A/form B	4/6	3ms			

Contact ratings

Туре	Contact	Load	Cycles
IEC 61810 ¹⁾			
RZL3-1A4.	A (NO)	16A, 250VAC, 85°C	50x103
RZL3-1C4.	C (CO)	16A, 250VAC, 85°C	10x10 ³
RZL3-1A4.	A (NO)	16A, 250VAC, 70°C	100x10 ³
RZL1-1A4	A (NO)	12A, 250VAC, 85°C	100x10 ³
RZL1-1A4	A (NO)	16A, 250VAC, 70°C	100x10 ³
RZL3-1A4.	A (NO)	8A, cosφ=0.4, 250VAC, 25°C	100x10 ³
RZL3-1C4.	B (NC)	8A, 250VAC, 25°C	100x10 ³
UL 508			
RZL3-1A4.	A (NO)	16A, 250VAC, 85°C	50x10 ³
RZL3-1C4.	C (CO)	16A, 250VAC, 85°C	10x10 ³
RZL3-1A4.	A (NO)	16A, 250VAC, 70°C	100x10 ³
RZL1-1A4	A (NO)	12A, 250VAC, 85°C	100x10 ³
RZL1-1A4	A (NO)	16A, 250VAC, 70°C	100x10 ³
RZL1/3-1A4.	A (NO)	1hp, 240VAC, 25°C	6x10 ³
RZL1/3-1A4.	A (NO)	1/2hp, 120VAC, 70°C	6x10 ³
1) ratings in progre	ess		

IV	lax	. C	C	le	oa	d	bre	ak	ing	g (ca	pa	aci	ity	,
300			N			П					Ш				
200		_	٨	+	Н	Н		_	Н	+	Щ	#		+	
				\setminus					res	isti	ve	loa	ad		
100			Ц	1	Щ	Ц			Ц	1	Щ	4		4	
F			Ħ	1	V	Ħ			\exists	+	Н	#		\mp	_
				#	1	Ų			\Box	#	ш	#		#	
50 -	-		Н	+	Н	H	$\overline{}$	\vdash	\vdash	+	Н	#		+	-
음 40⊢	\rightarrow	-	Н	+	Н	₩	\rightarrow	$\overline{}$	H	+	Н	₩	_	+	_
≥ ₃n∟				_	Ш	Щ			1	+	Щ	Щ		_	
oltage [VDC]												T	n	П	
쓸 2이는			Н	Ť	Ħ	Ħ			Н	Ť	Ш	#	Ħ	\top	

Coil Data		
Coil voltage range	5 to 48VDC	
Operative range, IEC 61810	2	
Coil insulation system according UL1446	class F	

Coil vers	sions, DC co	il			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	$\Omega \pm 10\%$	mW
L005	5	3,5	0,5	47	530
L006	6	4,2	0,6	67	530
L009	9	6,3	0,9	153	530
L012	12	8,4	1,2	272	530
L024	24	16,8	2,4	1086	530
L048	48	33,6	4,8	4347	530

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.

Insulation Data		
Initial dielectric strength		
between open contacts	1000V _{rms}	
between contact and coil	5000V _{rms}	
Clearance/creepage		
between contact and coil	≥10/10mm	
Material group of insulation parts	Illa	
Tracking index of relay base	PTI250V	


O.I. D.:					
Other Data					
Material compliance: EU RoHS/ELV, China RoHS compliance,					
Ambient temperature					
standard version	-40 to 70°C				
special applications	-40 to 85°C				
Category of environmental protection	1				
IEC 61810	RTII - flux proof; RTIII wash tight				
Vibration resistance (functional), 30 to	500Hz				
closing form A contact	>15g				
opening form A contact	>20g				
opening form B contact	>5g				
Shock resistance (destructive)	100g				
Terminal type	PCB-THT				
Mounting distance					
standard version	≥0mm				
Weight	10g				
Resistance to soldering heat THT					
IEC 60068-2-20	260°C/10s ²⁾				
Packaging/unit	tube/20 pcs., box/500 pcs.				
2) The use of foaming flux is not permitted.	·				




Power PCB Relay RZL (Continued)


Dimensions


12A/16A, pinning 3.5mm ²⁾





12A, 16A, pinning 5mm ²⁾







PCB layout / terminal assignment

Bottom view on solder pins

12A/16A, pinning 3.5mm ²⁾




16A, pinning 5mm




Recommended pcb hole for manual mounting: \emptyset 1.3mm

For automated mounting please ask for detailed drawing.







1 form C (CO) contact




1 form C (CO) contact




1 form C (CO) contact



S0163-BE





1 form A (NO) contact


2) For 1 Form C type, subject to develop as market requirement

S0163-BG

S0163-BC



Power PCB Relay RZL (Continued)



Product code	Version	Contacts	Contact material	Coil	Part number
RZL1-1A4-L012-R	12A/16A, pinning 3.5mm, flux proof	1 form A (NO)	AgNi 90/10	12VDC	2158100-4
RZL3-1A4-L012-R	16A, pinning 5mm, flux proof	1 form A (NO)		12VDC	1-2158100-6
RZL3-1A4-L024-R		1 form A (NO)		24VDC	1-2158100-7
RZL3-1C4-L012-R		1 form C (CO)		12VDC	2-2158100-2
RZL3-1C4-L024-R		1 form C (CO)		24VDC	2-2158100-3
RZL3-1A4-L012-W	16A, pinning 5mm, wash tight	1 form A (NO)		12VDC	4-2158100-0
RZL3-1C4-L024-W		1 form C (CO)		24VDC	4-2158100-7

This list represents the most common types and does not show all variants covered by this datasheet.

Other types on request