



# CAMBLOCK PLUS

## 5.08mm Pitch High Power Rising Clamp Terminal Blocks

CTBP0708

- 2 & 3 pole double interlocking mechanism for increased strength
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 2.5mm<sup>2</sup> (26-12AWG)
- Guided pin alignment
- Captive screw
-  &  approved



### SPECIFICATION

Rating	UL=20A/300V, VDE=20A/250V
Insulation resistance	500MΩ/500V
Withstand Voltage	AC2000V/1min
Contact Resistance	20mΩ (max)
Working Temperature	-40°C to 105+°C
Mouldings	UL94-V0 Flame retardant PA66
Pin/Terminal	Tin plated brass
Rising Clamp	Brass, nickel plated
Screw/Torque	M3 Steel, zinc plated 0.5Nm
Recommended PCB hole size	ø1.6mm

TYPE NO.	POLES	LENGTH
CTBP0708/2	2	10.16mm
CTBP0708/3	3	15.24mm
CTBP0708/4	4	20.32mm
CTBP0708/5	5	25.4mm
CTBP0708/6	6	30.48mm
CTBP0708/7	7	35.56mm
CTBP0708/8	8	40.64mm
CTBP0708/9	9	45.72mm
CTBP0708/10	10	50.8mm
CTBP0708/11	11	55.88mm
CTBP0708/12	12	60.96mm

