

IT18FL9L4

Article Number: 111-81907

Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Natural, 200/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number IT18FL9L4

Type IT18FL

Color Natural (NA)

- Features and Benefits**
- Identification plate feature allows bundles to be easily marked and identified.
 - Wire and cable harnesses can be secured and identified using just one product, which saves time.
 - Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.

Product Description HellermannTyton Identification cable ties feature an identification plate allowing wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Mounting method Identification ETIM Others

Short Description Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Natural, 200/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 18.0 lbs

Minimum Tensile Strength (Metric) 80.0 N

Length L (Imperial) 4.3 "

Length L (Metric) 110.0 mm

Fixation Method None

Identification Plate Position stands of bundle

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.81 "

Width W (Metric) 20.5 mm

Width W2 (Imperial) 0.1 "

Width W2 (Metric) 2.5 mm

Height H (Imperial) 0.35 "

Height H (Metric) 9.0 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 0.75 "

Bundle Diameter Max. (Metric) 19.0 mm

Outside Diameter Min. (Imperial) 0.059 "

Outside Diameter Min. (Metric) 1.50 mm

Outside Diameter Max. (Imperial) 0.75 "

Outside Diameter Max. (Metric) 19.00 mm

Logistics and Packaging

Quantity Per bag
Package Quantity (Metric) 200
Carton Quantity 10000

Material and Specifications

Material Polyamide 6.6 (PA66)
Material Shortcut PA66
Flammability UL94 V2
Halogenfree Yes
Operating Temperature -40°F to +185°F (-40°C to +85°C)
ROHS Compliant Yes
Certification/Specification UL
UL Listed (US and Canada) No
UL Recognized (US and Canada) Yes