

## RT250M9X2



**Article Number:** 131-75619

**Releasable Cable Tie, 22.3" Long, 250 lb Tensile Strength, PA66, Natural, 25/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** RT250M9X2

**Type** RT250M

**Color** Natural (NA)

- Features and Benefits**
- Special design offers a release feature for quick and easy access to wire bundles.
  - Head design provides high tensile strength with very low insertion force even after repeated use.
  - Buckle feature on head allows excess strap to be tucked away after installation.

**Product Description** HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Releasable Cable Tie, 22.3" Long, 250 lb Tensile Strength, PA66, Natural, 25/pkg

### Product Dimensions

**Minimum Tensile Strength (Imperial)** 250.0 lbs

**Minimum Tensile Strength (Metric)** 1115.0 N

**Length L (Imperial)** 22.3 "

**Length L (Metric)** 565.3 mm

**Fixation Method** None

**Identification Plate Position** none

**Releasable Closure** Yes

**Tie Closure** plastic pawl

**Variant** Inside Serrated

**Width W (Imperial)** 0.49 "

**Width W (Metric)** 12.5 mm

**Cable Tie Width Max. (Imperial)** 0.49 "

**Cable Tie Width Max. (Metric)** 12.5 mm

**Bundle Diameter Min. (Imperial)** 0.47 "

**Bundle Diameter Min. (Metric)** 12.0 mm

**Bundle Diameter Max. (Imperial)** 5.9 "

**Bundle Diameter Max. (Metric)** 150.0 mm

**Thickness T (Imperial)** 0.075 "

**Cable Tie Head Length (Imperial)** 0.88 "

**Cable Tie Head Width (Imperial)** 0.79 "

**Thickness T (Metric)** 1.9 mm

## Logistics and Packaging

---

<b>Quantity Per</b>	bag
<b>Package Quantity (Metric)</b>	25 Pieces
<b>Carton Quantity</b>	500
<b>Weight (Metric)</b>	13 kg

## Material and Specifications

---

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL94 V2
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL
<b>UL Listed (US and Canada)</b>	No
<b>UL Recognized (US and Canada)</b>	Yes