

T18MR9M4



Article Number: 113-00028

Screw Mount Tie, 18lb 4.3" Long, Max Bun Diameter .79", #4 Screw, PA66, Natural, 100/pkg



Download spec sheet

Base Data

| | |
|------------------------------|---|
| Local Order Number | T18MR9M4 |
| Type | T18MR |
| Color | Natural (NA) |
| Features and Benefits | <ul style="list-style-type: none"> • Mount design secures firmly on any #4 Screw • Screw mount style creates low insertion and high extraction force. |
| Product Description | Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting. |
| Short Description | Screw Mount Tie, 18lb 4.3" Long, Max Bun Diameter .79", #4 Screw, PA66, Natural, 100/pkg |

Product Dimensions

| | |
|---|-----------------|
| Minimum Tensile Strength (Imperial) | 18.0 lbs |
| Minimum Tensile Strength (Metric) | 80 N |
| Length L (Imperial) | 4.3 " |
| Length L (Metric) | 110.0 mm |
| Fixation Method | fixing hole |
| Identification Plate Position | none |
| Releasable Closure | No |
| Tie Closure | plastic pawl |
| Variant | Inside Serrated |
| Width W (Imperial) | 0.1 " |
| Width W (Metric) | 2.5 mm |
| Height H (Imperial) | 0.17 " |
| Height H (Metric) | 4.2 mm |
| Bundle Diameter Min. (Imperial) | 0.06 " |
| Bundle Diameter Min. (Metric) | 1.5 mm |
| Bundle Diameter Max. (Imperial) | 0.8 " |
| Bundle Diameter Max. (Metric) | 20.0 mm |
| Mounting Hole Diameter D (Imperial) | 0.12 " |
| Mounting Hole Diameter D (Metric) | 3.1 mm |
| Thickness T (Imperial) | 0.039 " |
| Mounting Hole Diameter D Max. (Metric) | 3.1 mm |
| Mounting Hole Diameter D Min. (Metric) | 3.1 mm |
| Thickness T (Metric) | 1.0 mm |

Logistics and Packaging

| | |
|----------------------------------|-------|
| Quantity Per | bag |
| Package Quantity (Metric) | 1000 |
| Carton Quantity | 10000 |

Material and Specifications

| | |
|--------------------------------------|----------------------------------|
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL94 V2 |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| ROHS Compliant | Yes |
| Certification/Specification | UL |
| UL Listed (US and Canada) | No |
| UL Recognized (US and Canada) | Yes |