

Surge Arrester

3-Electrode-Arrester

Series/Type: T83-A150X

Ordering code: B88069X9590B502

Date: 23.05.2002 Version: Issue 03

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, Alu-X, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PQSine, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, TFAP, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.



T83-A150X Surge Arrester

3-Electrode-Arrester

Ordering code: B88069X9590B502

DC spark-over voltage 1) 2) 4)		150	V
		± 20	%
Impulse spark-over at 100 V/µs		< 450 < 400	V
at 1 kV/µs	for 99 % of measured valuestypical values of distribution	< 550 < 500	V
Nominal impulse discharge current (wave 8/20 µs) 5) Single impulse discharge current (wave 8/20 µs) 5)		10 12,5	kA kA
Nominal alternating discharge current (50 Hz, 1 s) ⁵⁾ Alternating discharge current (50 Hz, 9 cycles) ⁵⁾		10 40	A A
Insulation resistance at 100 V _{dc} ⁴⁾		> 10	GΩ
Capacitance at 1 MHz ⁴⁾		< 1.5	pF
Transverse delay time 3)		< 0.2	μs
Arc voltage at 1 A Glow to arc transition current Glow voltage		~ 10 ~ 1.0 ~ 60	V A V
Weight		~ 2	g
Operation and storage temperature		-40 +90	°C
Climatic category (IEC 60068-1)		40/ 90/ 21	
Marking, red		EPCOS 150 YY O 150 - Nominal voltage YY - Year of production O - Non radioactive	

At delivery AQL 0.65 level II, DIN ISO 2859

Terms in accordance with ITU-T Rec. K.12 and DIN 57845/VDE0845

AB E / AB PM Issue 03, 23.05.2002

²⁾ In ionized mode


³⁾ Test according to ITU-T Rec. K.12
4) Tip or ring electrode to center electrode
5) Total current through center electrode, half value through tip respectively ring electrode.



Surge Arrester T83-A150X

3-Electrode-Arrester

Ordering code: B88069X9590B502



Not to scale

Dimensions in mm

Non controlled document

AB E / AB PM Issue 03, 23.05.2002

[©] EPCOS AG 2002. Reproduction, publication and dissemination of this data sheet, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.