


DATA SHEET N° DS/022	TRASP SYSTEM ADHESIVE TAG	DATE: 12/12/2006
--------------------------------	--	----------------------------

PICTURE



REFERENCE ITEM CODE

140/10 - 140/12MC - 140/15 - 140/15MC - 140/18 - 140/18MC - 140/23 - 140/30 - 140/MT

APPLICATION

THESE ITEMS PROVIDE A SIMPLE METHOD FOR CARRYING THE MARKER IN CASE OF DIFFICULT SURFACES

PHYSICAL PROPERTIES

MATERIAL	P.V.C.
COLOR	WHITE (RIGID PART) - CLEAR (RECESS)
OPERATIVE TEMPERATURE	- 50 ÷ +60 °C (-58 ÷ +140 °F)
FIRE RESISTANCE	CLASS VO IN COMPLIANCE WITH UL -94 NORMS
WATERPROOF	☺
OIL RESISTANT	☺
DUST RESISTANT	☺
ACID RESISTANT	☺
TOXIN FREE	PCB, PCT, PBB, PBDO, VC (MAX. 1 PPM)

ADHESIVE PHYSICAL PROPERTIES

ADHESIVE MASS	MODIFIED ACRYLIC
APPLICATION TEMPERATURE	> 10 °C
THICKNESS	0,4 mm 0,016 inch
TENSILE STRENGTH [N/25 mm]	22
ELONGATION %	300

ITEM CODE	CUT LENGTH (L)	TAGS PER PACK
140/10	10 mm / 0,39 inch	500 PIECES
140/12MC	12 mm / 0,47 inch	3000 PEZZI
140/15	15 mm / 0,59 inch	500 PIECES
140/15MC	15 mm / 0,59 inch	5000 PIECES
140/18	18 mm / 0,71 inch	200 PIECES
140/18MC	18 mm / 0,71 inch	3000 PIECES
140/23	23 mm / 0,91 inch	200 PIECES
140/30	30 mm / 1,18 inch	200 PIECES
140/MT	0,5 m / 19,7 inch	20 BARS

NOTES:

Document Married	REVIEWED, APPR. BY:	DATE:	REVISION ISSUE	PAGES
78-8127-9071-1				1 of 1