

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000046](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: Mini-Fit® Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 22-28 AWG, Reel

Documents:

Drawing (PDF)	Packaging Specification PK-5556-001 (PDF)
Product Specification PS-5556-001 (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-5556-002 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit®
UPC	800753627710

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	123.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data


Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Old Part Number	5556T2
-----------------	--------

Reference - Drawing Numbers

Packaging Specification	PK-5556-001
Product Specification	PS-5556-001 , PS-5556-002 , RPS-30067-001 , RPS-30067-002 , RPS-5557-031
Sales Drawing	SD-5556****
Test Summary	TS-5556-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[5556](#) Series

Mates With

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

Use With

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [5559](#) Mini-Fit Jr.™ Plug Housing, Dual Row

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

T2 Terminator™	<u>0639102700</u>
for insulation OD	
1.30-1.50mm - 22-28	
AWG	
T2 Terminator™	<u>0639123800</u>
for insulation OD	
0.95-1.08mm - 22-28	
AWG	
Hand Crimp Tool for	<u>0638191000</u>
Crimp Terminals	
T2 Terminator™	<u>0639120200</u>
for insulation OD	
1.10-1.30mm - 22-28	
AWG	
Extraction Tool	<u>0011030044</u>
FineAdjust™	<u>0639002700</u>
Applicator for	
Insulation OD	
1.30-1.50mm, 22-28	
AWG Wire	
FineAdjust™	<u>0639020200</u>
Applicator for	
Insulation OD	
1.10-1.30mm - 22-28	
AWG	
FineAdjust™	<u>0639023800</u>
Applicator for	
Insulation OD	
0.95-1.08mm - 22-28	
AWG	

Japan

Description	Product #
Hand Extraction Tool	<u>0570316000</u>
Applicator for M21 1A	<u>0570383000</u>
Bench Press, 22-28	
AWG Wire	

This document was generated on 01/29/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION