

FPHS Series

Polyolefin Heat Shrink Tubing

pro-POWER



Description:

The FPHS series heat shrink tubing offers an outstanding balance of electrical, physical and chemical properties for a wide variety of industrial and military applications. FPHS is made of very flexible, heat-shrinkable polyolefin which is mechanically tough and chemically resistant.

Specifications:

Shrink Ratio	: 3:1
Colour	: Black
Shrink Temperature	: 100°C(212°F)

Typical Properties:

Physical

Tensile Strength	: 2,600 PSI
Ultimate Elongation	: 400%
Longitudinal Change	: ±5%
Secant Modulus (2%)	: 8,700 PSI
Specific Gravity	: 1.29
Heat Aging (168 hrs @ 158°C)	: Elongation (350%)
Heat Shock (4 hrs @ 250°C)	: No dripping, (4 hrs @ 250°C) cracking, or flowing
Low Temperature Flexibility (4 hrs @ -55°C)	: No Cracking
Water Absorption	: 0.2%
Flammability	: Self extinguishing
Operating Temperature	: -55°C to +135°C (-67°F to +275°F)
*Flexibility	: 3

Electrical

Dielectric Strength	: 700V/mil
Volume Resistivity	: 10 ¹⁵ Ω-cm

Chemical

Corrosive Effect	: Non-corrosive
Solvent Resistance	
Tensile Strength	: 1,100 PSI
Dielectric Strength	: 400V/mil
Fungus Resistance	: Inert

Applicable Specifications: MIL-DTL-23053/5 Class 1

*Flexibility : The materials are rated on a scale of 1 to 10.
1 = most flexible and 10 = most rigid

FPHS Series

Polyolefin Heat Shrink Tubing



Dimension Table

Dimensions				Standard Packages		
Size (Inches)	Expanded I.D. (Min.) (Inches)	Recovered I.D. (Max.) (Inches)	Recovered Nominal Wall Thickness (Inches)	4 Foot Lengths (+1", -0")		
				Total Footage	QTY.	Part Number
1/16	0.059	0.02	0.018	100 FT	25	FPHS-004-4025-BLK
1/8	0.118	0.039	0.022			FPHS-008-4025-BLK
1/4	0.236	0.079	0.026			FPHS-016-4025-BLK
3/8	0.354	0.118	0.03			FPHS-024-4025-BLK
1/2	0.472	0.157	0.03	20 FT	5	FPHS-032-4005-BLK
3/4	0.709	0.236	0.03			FPHS-048-4005-BLK
1	0.945	0.315	0.039			FPHS-064-4005-BLK
1-1/2	1.535	0.512	0.045			FPHS-096-4005-BLK

Dimensions				Standard Packages		
Size (Inches)	Expanded I.D. (Min.) (Inches)	Recovered I.D. (Max.) (Inches)	Recovered Nominal Wall Thickness (Inches)	6 Inch Lengths (±125")		
				Total Footage	QTY.	Part Number
1/16	0.059	0.02	0.018	14 FT	28	FPHS-004-6028
1/8	0.118	0.039	0.022	12 FT	24	FPHS-008-6024
1/4	0.236	0.079	0.026	10 FT	20	FPHS-016-6020
3/8	0.354	0.118	0.03	8 FT	16	FPHS-024-6016
1/2	0.472	0.157	0.03	7 FT	14	FPHS-032-6014
3/4	0.709	0.236	0.03	6 FT	12	FPHS-048-6012
1	0.945	0.315	0.039	4 FT	8	FPHS-064-6008
1-1/2	1.535	0.512	0.045	2.5 FT	5	FPHS-096-6005

Part Number Table

Description	Part Number
FPHS Series Polyolefin Heat Shrink Tubing 4 Foot Lengths	FPHS-004-4025-BLK
	FPHS-008-4025-BLK
	FPHS-016-4025-BLK
	FPHS-024-4025-BLK
	FPHS-032-4005-BLK
	FPHS-048-4005-BLK
	FPHS-064-4005-BLK
	FPHS-096-4005-BLK

Description	Part Number
FPHS Series Polyolefin Heat Shrink Tubing 6 Inch Lengths	FPHS-004-6028
	FPHS-008-6024
	FPHS-016-6020
	FPHS-024-6016
	FPHS-032-6014
	FPHS-048-6012
	FPHS-064-6008
	FPHS-096-6005

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.