

111-01125



Article Number: 111-01125

High Temp Cable Tie, 15.2" Long, 120lb Tensile Strength, ETFE, Blue, 50/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 111-01125

Type T120R

Color Blue (BU)

- Features and Benefits**
- ETFE cable ties provide excellent resistance to chemicals, radiation, high temperatures and UV exposure.
 - Inside serrations allows for strong hold on cables and wire bundles.
 - Head design provides high tensile strength with very low insertion force.
 - Bent tail ensures a quick and simple installation.

Product Description HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description High Temp Cable Tie, 15.2" Long, 120lb Tensile Strength, ETFE, Blue, 50/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 120.0 lbs

Minimum Tensile Strength (Metric) 535.0 N

Length L (Imperial) 15.2 "

Length L (Metric) 387.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.29 "

Width W (Metric) 7.4 mm

Bundle Diameter Min. (Imperial) 0.59 "

Bundle Diameter Min. (Metric) 15.0 mm

Bundle Diameter Max. (Imperial) 4.1 "

Bundle Diameter Max. (Metric) 105.0 mm

Thickness T (Imperial) 0.075 "

Cable Tie Head Length (Imperial) 0.47 "

Cable Tie Head Width (Imperial) 0.51 "

Thickness T (Metric) 1.9 mm

Logistics and Packaging

Package Quantity (Metric) 50 Pieces
Carton Quantity 2000 Pieces
Weight (Metric) 5.2 kg

Material and Specifications

Material Ethylenterafluoroethylene - (E/TFE)
Material Shortcut E/TFE
Flammability UL94 V0
Operating Temperature -112°F to +338°F (-80°C to +170°C)
ROHS Compliant Yes
Certification/Specification Det Norske Veritas
UL Listed (US and Canada) No
UL Recognized (US and Canada) Yes