

126-00042



Article Number: 126-00042

Arrowhead Wing Push Mount Tie, 4.5" Long, 18lb, Panel Thickness 0.19"- 0.22", PA66, Black, 1,000/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 126-00042

Type T18RWPM

Color Black (BK)

- Features and Benefits**
- Easy and quick insertion ideal for production environment.
 - Tie "clicks" into place upon final installation signaling installer insertion is complete.
 - Arrowhead style mount provides low insertion and high extraction force.

Product Description Arrowhead Wing Push Ties design helps stabilize the tie in high vibration applications. This can be used on sheet metal, wood, and cast iron.

Short Description Arrowhead Wing Push Mount Tie, 4.5" Long, 18lb, Panel Thickness 0.19"- 0.22", PA66, Black, 1,000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 18.0 lbs

Minimum Tensile Strength (Metric) 80 N

Length L (Imperial) 4.5 "

Length L (Metric) 113.0 mm

Fixation Method Arrowhead

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.1 "

Width W (Metric) 2.5 mm

Width W2 (Imperial) 0.25 "

Width W2 (Metric) 6.4 mm

Height H (Imperial) 0.23 "

Height H (Metric) 5.8 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 0.86 "

Bundle Diameter Max. (Metric) 22.0 mm

Disc Diameter (Imperial) 0.5 "

Disc Diameter (Metric) 13.2 mm

Panel Thickness Max. (Imperial) 0.13 "

Panel Thickness Max. (Metric)	3.2 mm		
Panel Thickness Min. (Imperial)	0.06 "		
Panel Thickness Min. (Metric)	1.52 mm		
Mounting Hole Diameter D (Imperial)	0.19 - 0.22 "		
Mounting Hole Diameter D (Metric)	4.8 - 5.6 mm		
Mounting Hole Diameter D Min. (Imperial)	0.19 "		
		Mounting Hole Diameter D Max. (Imperial)	0.22 "
			Thickness T (Imperial)
			0.043 "
Mounting Hole Diameter D Max. (Metric)	5.6 mm		
		Mounting Hole Diameter D Min. (Metric)	4.8 mm
Thickness T (Metric)	1.1 mm		

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000
Carton Quantity	10000

Material and Specifications

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL94 V2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Certification/Specification	UL