

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015244745](#)
Status: **Active**
Overview: Disk Drive Power Connector
Description: 5.08mm Pitch Disk Drive Power Connection System Header, Vertical, Through Hole, 4 Circuits, Lead-Free, 3.58mm PC Tail Length, without PCB Locator Peg

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification


CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series [8981](#)
 Application Power, Wire-to-Board
 MolexKits Yes
 Overview [Disk Drive Power Connector](#)
 Product Name Disk Drive Power
 UPC 822348644537

Physical

Breakaway No
 Circuits (Loaded) 4
 Circuits (maximum) 4
 Color - Resin Black
 Durability (mating cycles max) 25
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Mated Height 24.00mm
 Material - Metal Phosphor Bronze
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 1.734/g
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 3.58mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 1.60mm
 Packaging Type Tray
 Pitch - Mating Interface 5.08mm
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Polarized to Mating Part Yes
 Polarized to PCB No
 Shrouded Fully
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -40°C to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[8981 Series](#)

Mates With

[15-24-4048 \(89814P\)](#) Disk Drive Power
 Connection System Female Crimp Housing
 with Terminal [02-08-1201 \(8980-3C\)](#) or
[02-08-1202 \(8980-3L\)](#)

Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 6.5A
Voltage - Maximum 250V AC

Solder Process Data

Duration at Max. Process Temperature (seconds) 010
Lead-freeProcess Capability SMC&WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 265

Material Info

Old Part Number A-8981-4V5-LF

Reference - Drawing Numbers

Sales Drawing SD-8981-4V5

This document was generated on 02/03/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION