

## MB29C2



**Article Number:** 151-00227

**Cable Tie Mount, 0.193" Hole Dia., 0.18" Max Tie Width, PA66, Natural, 100/pkg**



Download spec sheet

### Base Data

<b>Local Order Number</b>	MB29C2
<b>Type</b>	MB2
<b>Color</b>	Natural (NA)
<b>Features and Benefits</b>	<ul style="list-style-type: none"> <li>• For use with 18 through 50 pound cable ties to provide stability when securing bundles.</li> <li>• Low profile design offers use in space constrained areas.</li> <li>• Secures with a single screw providing quick installation.</li> </ul>
<b>Product Description</b>	HellermannTyton cable tie screw mounts are used with 18 through 50 pound cable ties to provide stability when securing bundles. The low profile design allows for use in space constrained areas. The mounts are installed quick and easy by securing a single screw.
<b>Short Description</b>	Cable Tie Mount, 0.193" Hole Dia., 0.18" Max Tie Width, PA66, Natural, 100/pkg

### Product Dimensions

<b>Length L (Imperial)</b>	0.81 "
<b>Length L (Metric)</b>	20.6 mm
<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Width W (Imperial)</b>	0.49 "
<b>Width W (Metric)</b>	12.5 mm
<b>Cable Tie Width Max. (Imperial)</b>	0.18 "
<b>Cable Tie Width Max. (Metric)</b>	4.6 mm
<b>Height H (Imperial)</b>	0.13 "
<b>Height H (Metric)</b>	3.3 mm
<b>Height H2 (Imperial)</b>	0.05 "
<b>Height H2 (Metric)</b>	1.7 mm
<b>Mounting Hole Diameter D (Imperial)</b>	0.193 "
<b>Mounting Hole Diameter D (Metric)</b>	4.9 mm
<b>Mounting Hole Diameter D Max. (Metric)</b>	4.9 mm
<b>Mounting Hole Diameter D Min. (Metric)</b>	4.9 mm

### Logistics and Packaging

<b>Quantity Per</b>	bag
<b>Package Quantity (Metric)</b>	100
<b>Carton Quantity</b>	15000

### Material and Specifications

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL94 V2
<b>Halogenfree</b>	Yes
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>UL Listed (US and Canada)</b>	No
<b>UL Recognized (US and Canada)</b>	No
<b>UL Recognized (US)</b>	No