

RO512

Article Number: 590-05120

Rite-On Self-Laminating Label Dispenser, .75" X .5" X 1.875", Vinyl, White, 150/RL



Download drawing



Download spec sheet

Base Data

Local Order Number RO512

Type RO512

Color White (WH)
Transparent (CL)

Features and Benefits

- Compact to easily fit in pants or shirt pockets.
- Dispenser can be reloaded over and over, making it cost effective to use.
- Dispenser edge allows easy removal of label liner.
- Dispenser protects labels from dirt and moisture before use, extending the life and quality of the labels.

Color Marking Field White (WH)

Product Description HellermannTyton's Rite-On Markers are made from a flexible vinyl film and used to mark wire and cable. The self-laminating labels have a clear tail which seals the legend under clear vinyl, maintaining the quality of the labels. The Rite-On markers are packaged in a reusable dispenser made from high impact plastic which is resistant to oils and grease.

Mounting method Identification ETIM Pasting / Stick

Short Description Rite-On Self-Laminating Label Dispenser, .75" X .5" X 1.875", Vinyl, White, 150/RL

Product Dimensions

Length L (Imperial) 0.5 "

Length L (Metric) 12.7 mm

Fixation Method Pasting / Stick

Self adhesive (Yes/No) Yes

Variant Roller form

Width W (Imperial) 0.75 "

Width W (Metric) 19.05 mm

Height H (Imperial) 0.5 "

Height H (Metric) 12.7 mm

Height H2 (Imperial) 1.875 "

Height H2 (Metric) 47.62 mm

Bundle Diameter Min. (Imperial) 0.26 "

Bundle Diameter Min. (Metric) 6.68 mm

Bundle Diameter Max. (Imperial) 0.33 "

Bundle Diameter Max. (Metric) 8.38 mm

Outside Diameter Min. (Imperial) 0.263 "

Outside Diameter Min. (Metric) 6.68 mm

Outside Diameter Max. (Imperial) 0.33 "

Outside Diameter Max. (Metric) 8.38 mm

Logistics and Packaging

Quantity Per	pack
Package Quantity	150
Package Quantity (Metric)	150
Carton Quantity	1

Material and Specifications

Material	Type 100, Vinyl (PVC), white (WH), self laminating
Material Shortcut	100
Adhesive Shortcut	Acrylic
Adhesive Operating Temperature	-51°F to +200°F (-46°C to +93°C)
Operating Temperature	-51°F to +200°F (-46°C to +93°C)
ROHS Compliant	Yes