



Spiral Wrap
T&B Catalog Number:

SRPE-250-0-C

UPC Number:

72849407580

Status:

Active

Description:

Spiral Wrap, Black Polyethylene for Temperatures up to 50 Degrees Celsius (122 F), Weather and Ultraviolet Resistant, Outside Diameter of 6.35mm (0.250 Inches), Pitch of 9.53mm (0.375 Inches), Nominal Wall Thickness of 1.14mm (0.045 Inches), 30.48m Reel (100 Feet)

Features

Perfect for protection of bundles from .063 to 7 inch diameters.

Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation, and rigidity.

Available in three materials.

General

| | |
|----------|--------------------------|
| Style | Reverse Cut |
| Material | Weatherable Polyethylene |
| Color | Black |

Dimension Information

| | |
|------------------------------------|-------|
| Pitch (inches) | 0.375 |
| Nominal Wall Thickness (inches) | 0.045 |
| Max. Wire Bundle Diameter (inches) | 2.000 |
| Min. Wire Bundle Diameter (inches) | 0.188 |
| Outside Diameter (inches) | 0.250 |

Specifications

| | |
|---------------------|----------|
| Flammability Rating | UL 94 HB |
|---------------------|----------|

Tooling

| | |
|-------------------|--------|
| Application Tools | SR-100 |
|-------------------|--------|

Packaging

| | |
|--------------------|----------------|
| T&B Order Multiple | 1 |
| T&B Inner Pack | 1 |
| Package in Units | 12 |
| Feet per Roll | 100 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 1.63 lbs. Each |

Notes

Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation and rigidity.

Certifications

| | |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

