

# Control cabinet feed-through - CUC-BH-M12D1PBK-S/R4BE - 1414398

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Control cabinet feed-through, M12, 4-pos., D-coded to RJ45 socket, socket entry: 180°, IP65/IP67


## Why buy this product

- Compact design
- 100 Mbps
- IP65/67
- UL



Ethernet

## Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 166759
Weight per Piece (excluding packing)	33.9 g
Custom tariff number	85366990
Country of origin	Germany
Product key	ABNZAC
Note	Made to Order (non-returnable)

## Technical data

### Mechanical characteristics

Insertion/withdrawal cycles	≥ 100
Cable exit	straight
Color	black

### Ambient conditions

Degree of protection	IP65/IP67
----------------------	-----------

### Material data

Flammability rating according to UL 94	V0
Housing material	PA
Contact material	Copper alloy

# Control cabinet feed-through - CUC-BH-M12D1PBK-S/R4BE - 1414398

## Technical data

### Electrical characteristics

Nominal voltage $U_N$	60 V
Nominal current $I_N$	0.5 A
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
Rated current	1 A

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

### eCl@ss

eCl@ss 8.0	27141134
------------	----------

### ETIM

ETIM 5.0	EC001283
----------	----------

## Approvals

### Approvals

#### Approvals


EAC / UL Listed / cUL Listed / cULus Listed

#### Ex Approvals

#### Approvals submitted

### Approval details

EAC
-----

UL Listed 	
Nominal current $I_N$	0.5 A
Nominal voltage $U_N$	60 V

# Control cabinet feed-through - CUC-BH-M12D1PBK-S/R4BE - 1414398

## Approvals

cUL Listed	
Nominal current I <sub>N</sub>	0.5 A
Nominal voltage U <sub>N</sub>	60 V


cULus Listed	
--------------	--

## Drawings

Explosion drawing

Dimensional drawing



Exploded drawing



Panel cutout

Dimensional drawing

Circuit diagram



Panel cutout

Circuit diagram