

**QOB Bolt-On Circuit Breakers [1]**

**Table 9.16: QOB-GFI, QOB-EPD, and QOB-EPE Circuit Breakers**

Ampere Rating [2]	One-pole	Two-pole—Common Trip	Three-pole—Common Trip	
	Catalog No.	Catalog No.	Catalog No.	Catalog No.
<b>QOB-GFI—QOB Qwik-Gard™ Circuit Breaker With Ground Fault Circuit Interrupter—UL Class A 4–6 mA People Protection. [3]</b>				
	120 Vac—10 k AIR	120/240 Vac—10 k AIR	208Y/120 Vac—10 k AIR	
15 A	QOB115GFI	QOB215GFI	QOB315GFI	
20 A	QOB120GFI	QOB220GFI	QOB320GFI	
25 A	QOB125GFI	QOB225GFI	—	
30 A	QOB130GFI	QOB230GFI	QOB330GFI	
40 A	—	QOB240GFI	QOB340GFI	
50 A	—	QOB250GFI	QOB350GFI	
60 A	—	QOB260GFI [4]	—	
<b>QOB-VHGF [5]</b>				
	120 Vac—22 k AIR			
15 A	QOB115VHGF			
20 A	QOB120VHGF			
25 A	QOB125VHGF			
30 A	QOB130VHGF			
<b>QOB-EPD—QOB Equipment protection circuit breakers with UL Listed 30 mA (EPD) or 100 mA (EPE) equipment protection.</b>				
	120 Vac—10 k AIR	120/240 Vac—10 k AIR	240 Vac—10 k AIR	
15 A	QOB115EPD	QOB215EPD	QOB315EPD [6]	QOB315EPE [6]
20 A	QOB120EPD	QOB220EPD	QOB320EPD [6]	QOB320EPE
25 A	QOB125EPD	QOB225EPD	—	—
30 A	QOB130EPD	QOB230EPD	QOB330EPD [6]	QOB330EPE [6]
40 A	—	QOB240EPD	QOB340EPD [6]	QOB340EPE [6]
50 A	—	QOB250EPD	QOB350EPD [6]	QOB350EPE [6]
60 A	—	QOB260EPD	—	—
<b>QOB-VHEPD</b>				
	120 Vac—22 k AIR			
15 A	QOB115VHEPD			
20 A	QOB120VHEPD			
25 A	QOB125VHEPD			
30 A	QOB130VHEPD			
<b>QOB-HM—High magnetic trip circuit breakers</b>				
15 A	QOB115HM [7]			
20 A	QOB120HM [7]			
<b>QOB-K—Key operated QOB circuit breakers [8]</b>				
	120 Vac—10 k AIR			
10 A	QOB110K			
15 A	QOB115K			
20 A	QOB120K			
25 A	QOB125K			
30 A	QOB130K			

**Table 9.17: Standard Interrupting QOB 10,000 AIR Circuit Breakers**

Ampere Rating [2]	One-pole	Two-pole—Common Trip	Two-pole—Common Trip [9]	Three-pole—Common Trip
	Catalog No.	Catalog No.	Catalog No.	Catalog No.
<b>QOB Bolt-On</b>				
	120 Vac—10 k AIR 48 Vdc—5 k AIR	120/240 Vac—10 k AIR 48 Vdc—5 k AIR [10]	240 Vac—10 k AIR	240 Vac—10 k AIR 48 Vdc—5 k AIR [10]
10 A	QOB110	QOB210	—	QOB310
15 A	QOB115 [7] [11]	QOB215 [11]	QOB215H	QOB315 [11]
20 A	QOB120 [7] [11]	QOB220 [11]	QOB220H	QOB320 [11]
25 A	QOB125 [11]	QOB225 [11]	QOB225H	QOB325 [11]
30 A	QOB130 [11]	QOB230 [11]	QOB230H	QOB330 [11]
35 A	QOB135 [11]	QOB235 [11]	—	QOB335 [11]
40 A	QOB140 [11]	QOB240 [11]	QOB240H	QOB340 [11]
45 A	QOB145 [11]	QOB245 [11]	—	QOB345 [11]
50 A	QOB150 [11]	QOB250 [11]	QOB250H	QOB350 [11]
60 A	QOB160 [11]	QOB260 [11]	QOB260H	QOB360 [11]
70 A	QOB170 [11]	QOB270 [11]	QOB270H	QOB370 [11] [10]
80 A	—	QOB280 [11] [10]	QOB280H	QOB380 [11] [10]
90 A	—	QOB290 [11] [10]	QOB290H	QOB390 [11] [10]
100 A	—	QOB2100 [11] [10]	QOB2100H	QOB3100 [11] [10]

[1] For QO plug-on circuit breakers, see the tables starting on Digest page 7-11.

[2] 10–30 A circuit breakers are suitable for use with 60 °C or 75 °C conductors. 35–60 A circuit breakers are suitable for use with 75 °C conductors.

[3] Do not connect to more than 250 feet of load conductor for the total one-way run to prevent nuisance tripping.

[4] Suitable only for feeding 240 Vac and 208 Vac two-wire loads. Does not contain load neutral connection.

[5] Recommended for applications where high initial inrush may occur and for individual dimmer applications.

[6] See note in Instruction Bulletin when using in an enclosure with a QO403 or QON prefix.

[7] UL Listed as SWD (switching duty) rated suitable for switching 120 Vac fluorescent lighting loads.

[8] Available in single pole construction and can be mounted in any single pole space which will accept a standard QOB. These circuit breakers can be turned ON or OFF or RESET with a special key (Catalog No. QOK10) included with the circuit breaker. These circuit breakers are UL Listed and available as shown in the table.

[9] UL Listed 5,000 AIR on 3Ø corner grounded delta systems.

[10] DC Rating is not available on indicated products.

[11] UL Listed as HACR type for use with air conditioning, heating, and refrigeration equipment having motor group combinations and marked for use with HACR type circuit breakers.