

PRODUCT DATA SHEET

10mm Capped Ultra High Brightness Neon Lamp

Product Ref. :8UHR220-1
Sheet : 1 of 1

GENERAL DESCRIPTION


10mm EX10 capped lamp incorporating an ultra high brightness neon lamp type 12.5/25UHB with a 68 Kohm series resistor for 230V ac operation.

BATCH AND PACKING DETAILS

Neon lamps to be packed in 100s in polythene bags. Each bag shall have a label showing type and batch number or date code.

The supplier is to provide test data qualifying the product to this specification if requested to do so.

OUTLINE DRAWING SHOWING CONSTRUCTION



Dimensions in mm

Notes

- 1) Neon lamp to be in conformance with Purchase Specification for type 12.5/25UHB.
- 2) Shape of lens moulding may differ from that shown in drawing, but lamp dimensions must be met.
- 3) Lamps to be checked for light-up at 230V ac.
- 4) Caps to be indented "8UHR220 CML" around rim near top edge in 3/64" (1.2mm) high block letters.

ISSUE NO.	ISSUE DATE	TECHNICAL	QUALITY	SALES	PURCH	C.NOTE NO.
1	09/03/05	Approved				-