# HellermannTyton

## 309-65235



Article Number: 309-65235

Heat Shrink Tubing, 4FT-Stick, 2:1, 4.0", 102/50.8 dia., Polyolefin, Yellow, 2/pkg

RoHS

#### **Base Data**

Local Order Number 309-65235

Type TFN21-ST 102/50.8 YE

Color Yellow (YE)

Features and Benefits • Thin, 2 to 1 shrink ratio tubing provides insulation and abrasion protection for wires and cables.

• Flammability rating of UL224 VW-1 for use in applications requiring the highest degree of flame protection (excludes

• Flexible-yet-durable material resists most common oils, chemicals and fluids.

· Available in a variety of diameters and colors for identifying and marking wires and cables.

· Available in mini reels, bulk reels, and sticks for small to large volume applications.

Product Description TFN21 is a highly flexible thin wall heat shrink tubing with a 2 to 1 shrink ratio and excellent flame retardant properties. In addition to providing insulation and abrasion protection for wires and cables, the polyolefin material also offers resistance to oils, solvents and chemicals. Available in mini reels, bulk reels and sticks, for small to large

volume applications.

Short Description Heat Shrink Tubing, 4FT-Stick, 2:1, 4.0", 102/50.8 dia., Polyolefin, Yellow, 2/pkg

#### **Product Dimensions**

Length L2 (Imperial) 4.0 ft

Length L2 (Metric) 1.22 m

Printable (Yes/No) Yes

Shrink Ratio 2:1

Tensile Strength (MPa) 14 MPa

**Trade Size** 

Variant Thin-Wall

Volume Resistance (Ohm cm) 10 $^{\circ}$ I  $\Omega$  cm

Nominal Diameter (Imperial) 4"

Nominal Diameter (Metric) 102 mm

Wall Thickness WT (Imperial) .053 "

Wall Thickness WT (Metric) 1.35 mm

Recovered Diameter d (metric) 50.8 mm

Recovered Diameter d (imperial) 2.0 "

Supplied Diameter D (metric) 102 mm

Supplied Diameter D (imperial) 4.0 "

### **Logistics and Packaging**

Quantity Per pack

Package Quantity 2

# **Material and Specifications**

Material Polyolefin, cross-linked (PO-X)

Material Shortcut PO-X

Dielectric Strength (Metric) 20 kV/mm

Elongation at break 600%

Flammability UL224 VW-1

Halogenfree No

Shrink Temperature +212 °F (+100 °C)

**Operating Temperature** -67°F to +275°F (-55°C to +135°C)

ROHS Compliant Yes

Certification/Specification UL224 125 °C 600V VW-1

CSA

UL Recognized (US) Yes