

Professional HD-IP 4MP Vandal WDR H265 Mini IR Dome Camera



X2C4000MP

- 4 Megapixel Resolution
- 3.6mm (78°) Lens
- 15m Smart IR Night Vision
- H265 Video Compression
- PoE Compatible
- Smartphone Remote Access



Features

Professional HD-IP Mini IR Dome Camera, supplied in a low-profile discreet dome housing. A high quality 3.6 mm lens for a 78° viewing angle with high power LEDs allowing night vision up to 15 metres.

The 4 Megapixel (2288 x 1712) CMOS Sensor supplied in the X2C4000MP achieves a resolution approximately nine times that of a conventional camera. This makes it possible to cover nine times the monitoring area, the image quality being the same. In addition, when captured images are enlarged the detail is much clearer.

Technical Specifications

X2C4000MP

Brand	XVISION
Model Number	X2C4000MP
Style	HD Vandal Dome Camera
Weather Resistant	Yes (IP66 Rated)
Vandal Resistant	Yes
Motorised Panning	No
Motorised Tilting	No
Digital Zoom	No
Audio	No
Mounting Type	Wall or Ceiling
Dimensions (WxHxD) mm	100x80x100
Weight (kg)	0.7
Image Sensor	1/2.9" Sony CMOS
Resolution	4 Megapixel
Minimum Illumination	0.001 Lux
Night Vision	15m
Other Features	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris DNR (Digital Noise Reduction), WDR (Wide Dynamic Range)
Lens	3.6mm
Viewing Angle	78°
Video Compression	H265
Video Streams	1024Kbps-6144Kbps
Stream Types	Complex Stream/Video Stream
Resolution & Frame Rates	1228x1712 @25fps
Network Connection	RJ45 Socket (10/100 Base-T)
WiFi Support	No
Network Protocols	TCP/IP, UDP, HTTP, DHCP, RTP/RTSP, DNS, DDNS, NTP, PPPoE, UPNP, SMTP
Browser Support	Internet Explorer
Mobile Phone Support	Android, iPhone
User Authentication	Yes
Simultaneous Viewers	10
Power Over Ethernet	Yes
Operating Voltage	12V DC
Power Consumption	<5W
Easy Fit	Yes (Optional Ethernet Over Mains Adaptor)
Motion Detection	No
Presets	No
Guard Tours	No
Email Alerts	Yes
On-Board Recording	No
Alarms	No
Multi-Camera Software	Yes

All specifications shown are subject to change without notice, please confirm up-to-date details when ordering. All network specifications and recording times are based upon theoretical scenarios. Actual performances will vary depending on external factors. No liability will be accepted by Y3K for any errors or omissions in this information. All relevant trade marks acknowledged. © Y3K (Europe) Limited 2015

■ DISTRIBUTED BY

