Product Specification S6079C Rev 1.0

Now you're connected!

About Amphenol Commercial Products

Amphenol's commercial connector products are used in a variety of end user applications including networking, telecom, server & computer, storage & HDD, consumer electronics and entertainment, professional audio & Industrial & Military/Aerospace.

Related Products

RJE72




P/N RJE72-188-11353 SHOWN SINGLE PORT, 8 POSITION, WITH SHIFLD AND LFDs

RJE45




P/N RJE45-X385-01 SHOWN SINGLE PORT, 8 POSITION, WITH SHIFLD AND LEDS

RJE71



P/N RJE71-188-1452 SHOWN SINGLE PORT, 8 POSITION, WITH SHIELD AND LEDS



Overview

This product specification defines the general use and performance parameters for Amphenol's RJE48 series of modular jacks.

Availability: Single port & four portconnectors available with a wide variety of LED and shielding options.

Usage

The RJE48 series of modular jacks meet CAT5e performance per EIA-568-C.2. It supports Gigabit Ethernet Protocols. Shielding available for increased EMI performance and LEDs for Link Activity and Network Speed verification.

Applications

Intended for use in applications such as: Networking & Telecom

- Wireless (WiMAX)
- Network servers
- Hubs, routers, switches

Office & Home Equipment

- PC's, Laptops, Copiers/Printers
- Telephones, modems
- Surge Protectors
- ATMs, Vending Machines

Consumer Goods

- Security Systems
- Set Top Boxes
- Video Game Systems

Miscellaneous

- Multi-Media Equipment
- Industrial Equipment
- POS Terminals

Now you're connected!

About Amphenol Commercial Products

Amphenol's commercial connector products are used in a variety of end user applications including networking, telecom, server & computer, storage & HDD, consumer electronics and entertainment, professional audio & Industrial & Military/Aerospace.

Related Products

RJULE



P/N RJULE-4X182-01 SHOWN SINGLE PORT REGULAR MOUNT, STANDARD SHIELD WITH SMT

FRJAE



P/N FRJAE-418 SHOWN SINGLE PORT, 8 POSITION, WITH FERRITE FILTER AND SHIELD (FRONT TABS)

RJLSE



P/N RJLSE-4X181-01 SHOWN SINGLE PORT, 8 POSITION, WITH SURFACE MOUNT AND SHIELD

Electrical Characteristics

Contact resistance: $20 \text{ m}\Omega \text{ max}$.

Insulation resistance: $500 \text{ M}\Omega$ minimum at 500 V DC for 2 minutes max.

Current rating: 1.25 Amps Voltage rating: 125 Volts AC

DWV 1000 VAC, 60 Hz. 1 min.

LED forward DC current: 20mA typical

LED forward Voltage: 1.9 Volts max. @ 2mA (for single colors)

2.6 Volts max. @ 20mA (for Bi-colors)

LED reverse voltage: 5 Volts minimum

LED light intensity: 0.4 to 1.5 mcd @ 2mA (for single colors)

0.5 mcd min. @ 2mA (for Bi-colors)

LED wave length: Yellow: 587± 7 nm measured @ 20mA

Green: 565 ± 6 nm measured @ 20mA Red: 625 ± 5 nm measured @ 20mA

Frequency MHz	Near-end Crosstalk dB Min.	Return Loss dB Min.	Attenuation dB Max.
1.0	65	30	0.1
4.0	65	30	0.1
8.0	64.9	30	0.1
10.0	63	30	0.1
16.0	58.9	30	0.2
20.0	57	30	0.2
25.0	55	30	0.2
31.25	53.1	30	0.2
62.5	47.1	24.1	0.3
100.0	43	20	0.4

Mechanical Characteristics

Mating connector insertion force: 5.0 lbs. Maximum. Mating connector pull retention force: 20 lbs Minimum.

Durability: 750 mating & unmating cycles Operating temperature: -55° C to +85° C Recommended soldering temperature:

Wave soldering peaked at 260° C for 5 seconds maximum.

Amphenol Canada Corp. 605 Milner Avenue Toronto, Ontario, Canada, M1B 5X6 +1 416 291 4401

Copyright © Amphenol Corporation 2011 • All rights reserved

Amphenol

Page 2 of 3

www.amphenolcanada.com

Now you're connected!

About Amphenol Commercial Products

Amphenol's commercial connector products are used in a variety of end user applications including networking, telecom, server & computer, storage & HDD, consumer electronics and entertainment, professional audio & Industrial & Military/Aerospace.

Related Products

RJE72



P/N RJE72-188-11353 SHOWN SINGLE PORT, 8 POSITION, WITH SHIELD AND LEDs

RJE45



P/N RJE45-X385-01 SHOWN SINGLE PORT, 8 POSITION, WITH SHIELD AND LEDS

RJE71



P/N RJE71-188-1452 SHOWN SINGLE PORT, 8 POSITION, WITH SHIELD AND LEDS

Material Requirements

RJE48 connectors are RoHS compliant.

Unless otherwise specified, the materials for each component shall be:

Insulator:

High Temp thermoplastic. Complies with UL 94V-0, Black color

Contacts:

- Phosphor Bronze hard temper with gold thickness options (6μ", 15μ", 30μ", 50μ") over 50μ" minimum Nickel on contact mating area.
- 100μ" minimum matte tin plating on solder tails

Shield:

Stainless steel with tin dipped tails

LED:

Tin plating on LED tails

Available Documents

Drawing Numbers:

P-RJE48-188-1XX1 P-RJE48-488-1XX1 Single port Cat 5E Modular Jack, 8 Position, with LEDs and Shield. Four port Cat 5E Modular Jack, 8 Position, with LEDs and Shield.

Contact factory or Authorized Amphenol representative for additional configurations.

Amphenol Canada Corp. 605 Milner Avenue Toronto, Ontario, Canada, M1B 5X6 +1 416 291 4401

Copyright © Amphenol Corporation 2011 • All rights reserved

Amphenol

www.amphenolcanada.com

Page 3 of 3