



Meets EN 61340-5-1 and Packaging standard IEC 61340-5-3

- A. This foam has outstanding “pin insertion” properties. It is used to hold devices in place.
- B. Corrosion prone non-ferrous metals such as Zinc, Nickel etc are not corroded when in direct or vapour contact with these conductive foams, even at elevated temperature and humidity.

| Property | Value | Test Method |
|--|--|--|
| Density kg/m ³ | 35-55 | BS 4443 Pt 1 Method 2 |
| Tensile Strength kPa | 70 Minimum | BS 4443 Pt 1 Method 3A |
| Loss in Tensile Strength After Heat Ageing (%) | 30% Max Loss | BS 4443 Pt 1 Method 3A 140°C for 16 hours |
| Loss In Tensile Strength After Humidity Ageing (%) | 30% Max Loss | BS 4443 Pt 1 Method 3A 105°C for 3 hours |
| Volume Resistance (ohms) | 1 x 10 ² to < 1 x 10 ⁵ | IEC 61340-2-3 |
| Surface Resistance (ohms) | 1 x 10 ² to < 1 x 10 ⁵ | IEC 61340-2-3 |

Foam per EN 61340-5

“All generators of electrostatic charges, such as untreated plastic films, foams, synthetic fibres, adhesive tapes, etc., must be prohibited for use as intimate or proximity packaging material and should be kept away from the EPA (ESD Protected Area)”. (EN 61340-5-2 section 6)

Inserting terminals in conductive foam will bring all terminals to the same charge level or equipotential protecting the device from a discharge.

“There are two basic points which should be followed throughout:

- only minimal charge, field, or potential should be generated inside an EPA, or should be allowed to come into contact with, or into close proximity to, any ESDS [ESD sensitive items];
- where a charge, field or potential is obtained then it should be removed in a controlled manner.

The most efficient manner of following the two above mentioned basic points in most applications is to provide a resistive path ... between an equipotential point and operator, equipment and ESDS. This will allow a controlled current path and will prevent any potential build up.” (EN 61340-5-2 DD1 Methods)

| Item | Description |
|-----------|---|
| VER-26270 | Foam, Conduct, Pin-Insertion, 6 x 305 x 305mm, Pack of 10 |
| VER-26457 | Foam, Conduct, Pin-Insertion, 6 x 127 x 228mm |
| VER-27110 | Foam,Conductive Cushioning, 6 x 305 x 305mm, Pack of 10 |

Unless otherwise noted, tolerance ±10%
Specifications and procedures subject to change without notice.



Made in the
United Kingdom

Vermason

Conductive Pin-Insertion Foam

VERMASON
 UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,
 HERTS, SG6 2TD UK
 Phone: +44 (0) 1462-672005
 E-MAIL: Service@Vermason.co.uk, Internet: Vermason.co.uk

Drawing Number
VER-26270

DATE:
March 2016