

High Speed, High Accuracy Tester Installation, Operation and Maintenance



Made in the
United States of America and
United Kingdom



Figure 1. VER-29202 High Speed, High Accuracy Wrist Strap Tester




Figure 2. VER-28876 High Speed, High Accuracy Wrist Strap Test Station



Figure 3. VER-28877 High Speed, High Accuracy Wrist Strap / Footwear Test Station

Description

All models of the Vermason High Speed, High Accuracy Tester range comprise a digital test unit controlled by a programmable IC. They can test the efficiency of personnel grounding systems while being worn, by measuring the resistance in the circuit including the body of the operator. The instrument will indicate whether the resistance is in the ranges specified in EN 61340-5-1 using Annex A test method A.1.

“All personnel shall be grounded or equipotentially bonded ... when handling ESDs [ESD sensitive items]. When personnel are seated at ESD protective workstations, they shall be connected to ground via a wrist strap system” [EN 61340-5-1 1 clause 5.3.2 Personnel grounding]

“The operator shall wear the wrist strap in the normal position and plug the free end of the cord into the test apparatus. The hand contact plate shall be pressed to verify that the grounding systems resistance is within acceptable parameters. The test apparatus can be an integrated, commercially available tester or other Instrumentation that is capable of measuring resistance from 5.0×10^4 ohms to at least 1.0×10^8 ohms. The tester open-circuit voltage is typically between 9 V d.c. and 100 V d.c.” [EN 61340-5-1 Annex A Test method A.1 Measurement method for wrist strap testing]

Wrist Strap Test Frequency

“Wrist straps should be tested periodically. The frequency of testing, however, is driven by the amount of usage, wear and ESD risk exposure that can occur between tests. For example, what is the quantity of product handled between test periods?”

Typical test programs recommend that wrist straps that are used daily should be tested daily. However, if the products that are being produced are of such value that a guarantee of a continuous, reliable ground is needed then continuous monitoring should be considered or even required.” [CLC/TR 61340-5-2 User guide Wrist Strap clause 4.7.2.4.4 Test frequency] “Where continuous monitoring is used, no additional testing is required.” [EN 61340-4-1, per A.5.2]

NOTE 1: Electrical breakages within the cord can be checked by flexing the cord during measurement. If the resistance is still too high, dry skin might be the problem. Dry skin conditions can be resolved by applying moisturizing lotion on the wrist and repeating the resistance test again. The moisturizing lotion should be one that is compatible with process requirements and does not cause contamination.

NOTE 2: Metal expansion bracelet style wrist bands may trap moisture underneath and can be more effective for people with dry skin. [CLC/TR 61340-5-2 User guide Wrist Strap clause 4.7.2.4.3 Test procedure]

The Vermason High Speed, High Accuracy Tester is available in three models:

Item	Description
VER-29202	Wrist Strap Tester
VER-28876	Wrist Strap Test Station
VER-28877	Wrist Strap / Footwear Test Station

Packaging

Item VER-29202

- 1 High Speed, High Accuracy Wrist Strap Tester
- 1 9V Alkaline Battery
- 1 Certificate of Calibration

Item VER-28876

- 1 High Speed, High Accuracy Wrist Strap Tester
- 1 Wall Plate
- 1 9V Alkaline Battery
- 1 Certificate of Calibration

Item VER-28877

- 1 High Speed, High Accuracy Wrist Strap / Footwear Tester
- 1 Wall Plate
- 1 Foot Plate, Single Foot
- 1 9V Alkaline Battery
- 1 Certificate of Calibration

Installation

1. Insert the 9V battery into the tester.
2. If applicable install the tester at the desired location using the four mounting holes in the corners of the yellow wall plate.
3. If applicable set the foot plate below the tester.
4. If applicable connect the footwear lead at the bottom of the tester to the foot plate.

Operation

WRIST STRAP

1. Snap the coiled cord to the wristband and fit it snugly onto the wrist.
2. Connect the other end of the wrist cord to a matching termination on the tester.
3. Push and hold the test button until a result is displayed.

A green LED with buzzer indicates a PASS condition. A red LED indicates a FAIL condition.

Replace battery if the LOW BATTERY LED illuminates.

FOOTWEAR

1. ESD Footwear covers heel grounders, toe grounders and ESD shoes/boots
2. Place one foot on the foot plate and raise the other off the floor.
3. Push and hold the test button until a result is displayed.

A green LED with buzzer indicates a PASS condition. A red LED indicates a FAIL condition.

Replace battery if the LOW BATTERY LED illuminates.

4. Repeat Steps 2-3 for the other foot.

Calibration

A periodic check (once every 6 to 12 months) using a precision resistance box should be performed to verify proper operation.

The Vermason Calibration Unit (VER-28532) is available for the periodic testing of the High Speed, High Accuracy Testers.

The Calibration Unit can be used in the test location within a few minutes virtually eliminating downtime, verifying that the High Speed, High Accuracy Tester is operating within tolerances.

See VER-28532 for more information.



Figure 5. VER-28532 Calibration Unit

Specifications

Wrist Strap Limit:

750 kilohm - 35 megohm

Footwear Limit:

750 kilohm - 35 megohm

Accuracy:

±5%

Test Voltage:

24VDC

Dimensions:

Tester

146mm L x 91mm W x 33mm H

Wall Plate

300mm L x 600mm W x 3mm H

Foot Plate

420mm L x 220mm W

Weight:

0.3kg (including battery and wall plate)

Power Supply:

9V battery

Battery Life:

approximately 3,000 tests (3 seconds per test)

Limited Warranty

Vermason expressly warrants that for a period of one (1) year from the date of purchase, Vermason High Speed, High Accuracy Testers will be free of defects in material (parts) and workmanship (labour). Within the warranty period, a unit will be tested, repaired or replaced at Vermason's option, free of charge. Call Customer Service at 0044 (0) 1462 672005 for a Return Material Authorisation (RMA) and for proper shipping instructions and address. Any unit under warranty should be shipped prepaid to the Vermason factory. You should include a copy of your original packing slip, invoice, or other proof of purchase date. Warranty repairs will take approximately two weeks.

If your unit is out of warranty, Vermason will quote repair charges necessary to bring your unit to factory standards. Call Customer Service at 0044 (0) 1462 672005 for a Return Material Authorisation (RMA) and proper shipping instructions and address.

Warranty Exclusions

THE FOREGOING EXPRESS WARRANTY IS MADE IN LIEU OF ALL OTHER PRODUCT WARRANTIES, EXPRESSED AND IMPLIED, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE WHICH ARE SPECIFICALLY DISCLAIMED. The express warranty will not apply to defects or damage due to accidents, neglect, misuse, alterations, operator error, or failure to properly maintain, clean or repair products.

Limit of Liability

In no event will Vermason or any seller be responsible or liable for any injury, loss or damage, direct or consequential, arising out of the use of or the inability to use the product. Before using, users shall determine the suitability of the product for their intended use, and users assume all risk and liability whatsoever in connection therewith.