


B



C

D

E

3mm  
(0.11")

C


F

G

H

7mm  
(0.28")

21mm  
(0.83")



- A. Underwriters Laboratory Listing 90P1C.
- B. Compatible with Vermason Dual-Wire Continuous Monitors and other brands that accept a 3.5mm phono plug.
- C. Thermoplastic elastomer strain relief molded on.
- D. Relaxed retraction coiled cord reduces tug on wearer's wrist. Black PVC insulation. Break load average 13.6 kilograms (30 pounds).
- E. Dual T-3067 tinsel conductor. Consists of stranded polyester wrapped in copper. Equivalent to 29 gauge (cir mil and/or ohms).

- F. 1 megohm ( $\pm 5\%$ ) current limiting resistors on both conductors.
- G. Unique dual contact design is to be paired with a Vermason MagSnap 360™ Wristband (not included) for a superior electrical connection. The magnetic connection made with the coil cord meets the 1-5 pound perpendicular breakaway force requirement per ANSI/ESD S1.1 to prevent accidental disconnects while allowing the worker to untether when needed. Spring loaded center contact rated to 1 million cycles.
- H. Date coded with date of manufacture in compliance with ANSI/ESD S1.1.
- I. "MagSnap 360" logo molded in compliance with ANSI/ESD S1.1.

Meets required limits of EN 61340-5-1 and requirements of ANSI/ESD S1.1.

Item	Retracted Length		Extended Length	
	X	Y	Nominal	Max
VER-29511	305mm (12")	508mm (20")	183cm (6')	259cm (8.5')
VER-29512	610mm (24")	813mm (32")	366cm (12')	518cm (17')
VER-29513	762mm (30")	965mm (38")	457cm (15')	671cm (22')

U.S. Patent Pending

Unless otherwise noted, tolerance  $\pm 10\%$   
Specifications and procedures subject to change without notice.

## MAGSNAP 360 COILED CORD

# Vermason

**VERMASON**  
 UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH,  
 HERTFORDSHIRE, SG6 2TD, UNITED KINGDOM  
 PHONE: +44 (0) 1462-672005  
 E-MAIL: [Service@Vermason.co.uk](mailto:Service@Vermason.co.uk), INTERNET: [Vermason.co.uk](http://Vermason.co.uk)

**DRAWING  
NUMBER**  
 VER-29511

**DATE**  
 February  
 2016