


Capacitor, Tantalum, 2.2 uF, +/-10% Tol, 25 V



| Dimensions (mm) | | |
|-----------------|-----------|-----------|
| Symbol | Dimension | Tolerance |
| D | 2.79 | MAX |
| L | 7.37 | MAX |
| F | 0.51 | +/-0.05 |
| LL | 38.1 | +/-6.35 |

| Packaging Specifications | |
|--------------------------|------|
| Package Kind: | Bulk |
| Package Type: | Bag |
| Package Quantity: | 250 |

| General Information | |
|---------------------|-------------------|
| Supplier: | KEMET |
| Application: | General Purpose |
| Body Type: | Axial |
| Lead Type: | Un-insulated Wire |
| Termination Type: | Tin (Sn) |
| RoHS: | Yes |

| Specifications | |
|---------------------|-----------------------|
| Capacitance: | 2.2 uF |
| Tolerance: | +/-10% |
| Voltage: | 25 VDC (85C) |
| Voltage: | 21 VDC (125C Surge) |
| Voltage: | 0.25 V (125C Reverse) |
| Temperature Range: | -55/+125C |
| Resistance/ESR: | 6 Ohms (100kHz) |
| Leakage Current: | 0.5 uA |
| Dissipation Factor: | 3% |