


Capacitor, Tantalum, 22 uF, +/-10% Tol, 35 V



| Dimensions (mm) |           |           |
|-----------------|-----------|-----------|
| Symbol          | Dimension | Tolerance |
| D               | 7.11      | MAX       |
| L               | 13.46     | MAX       |
| F               | 0.64      | +/-0.05   |
| LL              | 38.1      | +/-6.35   |

| Packaging Specifications |      |
|--------------------------|------|
| Package Kind:            | Bulk |
| Package Type:            | Bag  |
| Package Quantity:        | 100  |

| General Information |                   |
|---------------------|-------------------|
| Supplier:           | KEMET             |
| Application:        | General Purpose   |
| Body Type:          | Axial             |
| Lead Type:          | Un-insulated Wire |
| Termination Type:   | Tin (Sn)          |
| RoHS:               | Yes               |

| Specifications      |                       |
|---------------------|-----------------------|
| Capacitance:        | 22 uF                 |
| Tolerance:          | +/-10%                |
| Voltage:            | 35 VDC (85C)          |
| Voltage:            | 28 VDC (125C Surge)   |
| Voltage:            | 0.35 V (125C Reverse) |
| Temperature Range:  | -55/+125C             |
| Resistance/ESR:     | 1.3 Ohms (100kHz)     |
| Leakage Current:    | 6.2 uA                |
| Dissipation Factor: | 6%                    |