


Capacitor, Tantalum, General Purpose Radial Conformal (Dipped), 10 uF, +/-20% Tol, 16 V, Lead Spacing=2.54 mm



Dimensions (mm)

Symbol	Dimension	Tolerance
D	5.5	
H	8.9	
F	0.5	+/-0.05
S	2.54	+/-0.38
LL	12.7	+/-1.26

Packaging Specifications

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1000

General Information

Supplier:	KEMET
Application:	General Purpose
Part Type Description:	General Purpose Radial Conformal (Dipped)
Body Type:	Radial Conformal
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications

Capacitance:	10 uF
Tolerance:	+/-20%
Voltage:	16 V (85C)
Voltage:	12 VDC (125C Surge)
Voltage:	0.16 V (125C Reverse)
Temperature Range:	-55/+125C
Leakage Current:	1.3 uA
Dissipation Factor:	6%