


Capacitor, Tantalum, General Purpose Radial Conformal (Dipped), 4.7 uF, +/-10% Tol, 35 V, Lead Spacing=3.18 mm



Dimensions (mm)

Symbol	Dimension	Tolerance
D	5.5	
W	6.35	+/-0.64
H	10.2	
F	0.5	+/-0.05
S	3.18	+/-0.38
LL	4.75	+/-0.81

Packaging Specifications

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1000

General Information

Supplier:	KEMET
Application:	General Purpose
Part Type Description:	General Purpose Radial Conformal (Dipped)
Body Type:	Radial Conformal
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications

Capacitance:	4.7 uF
Tolerance:	+/-10%
Voltage:	35 V (85C)
Voltage:	28 VDC (125C Surge)
Voltage:	0.35 V (125C Reverse)
Temperature Range:	-55/+125C
Leakage Current:	1.3 uA
Dissipation Factor:	5%