

KEMET Part Number: T491C476K016AT
(B45196H3476K309)

Capacitor, Tantalum, SMD, MnO₂, Molded, 47 uF, 6032, +/-10% Tol, 16 VDC (85C)



| Dimensions (mm) | | |
|-----------------|-----------|-----------|
| Symbol | Dimension | Tolerance |
| L | 6 | +/-0.3 |
| W | 3.2 | +/-0.3 |
| H | 2.5 | +/-0.3 |
| F | 2.2 | +/-0.1 |
| S | 1.3 | +/-0.3 |
| B | 0.5 | +/-0.15 |
| X | 0.1 | +/-0.1 |
| P | 0.9 | REF |
| R | 1 | REF |
| T | 0.13 | REF |
| A | 2.9 | MIN |
| G | 2.8 | REF |
| E | 2.4 | REF |

| Packaging Specifications | |
|--------------------------|-------------|
| Package Kind: | T&R |
| Package Size: | 7 in/180 mm |
| Package Quantity: | 500 |

| General Information | |
|------------------------|--------------------------------|
| Supplier: | KEMET |
| Application: | General Purpose |
| Part Type Description: | SMD, MnO ₂ , Molded |
| Construction: | Standard Chip-MnO ₂ |
| Body Type: | SMD Chip |
| Footprint: | 6032 |
| Weight: | 224.48 mg |
| RoHS: | Yes |

| Specifications | |
|-------------------------|--------------------|
| Capacitance: | 47 uF |
| Tolerance: | +/-10% |
| Voltage: | 16 VDC (85C) |
| Voltage: | 10.72 VDC (125C) |
| Temperature Range: | -55/+125C |
| Current/Ripple Current: | 332 mAmps (25C) |
| Current/Ripple Current: | 298.8 mAmps (85C) |
| Current/Ripple Current: | 132.8 mAmps (125C) |
| Resistance/ESR: | 1 Ohms (100kHz) |
| Failure Rate: | N/A |
| Leakage Current: | 7.5 uA |
| Dissipation Factor: | 6% |