


KEMET Part Number: T491X476K035AT
(B45196H6476K509)

Capacitor, Tantalum, SMD, MnO2, Molded, 47 uF, 7343, +/-10% Tol, 35 VDC (85C)



Dimensions (mm)

Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	4	+/-0.3
F	2.4	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	1.7	REF
R	1	REF
T	0.13	REF
A	3.6	MIN
G	3.5	REF
E	3.5	REF

Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500

General Information

Supplier:	KEMET
Application:	General Purpose
Part Type Description:	SMD, MnO2, Molded
Construction:	Standard Chip-MnO2
Body Type:	SMD Chip
Footprint:	7343
Weight:	652.04 mg
RoHS:	Yes

Specifications

Capacitance:	47 uF
Tolerance:	+/-10%
Voltage:	35 VDC (85C)
Voltage:	23.45 VDC (125C)
Temperature Range:	-55/+125C
Current/Ripple Current:	524 mAmps (25C)
Current/Ripple Current:	471.6 mAmps (85C)
Current/Ripple Current:	209.6 mAmps (125C)
Resistance/ESR:	0.6 Ohms (100kHz)
Failure Rate:	N/A
Leakage Current:	16.5 uA
Dissipation Factor:	6%