

Capacitor, Tantalum, SMD, MnO₂, Molded, Low ESR, 22 uF, 3528, +/-20% Tol, 10 VDC (85C)



Dimensions (mm)

Symbol	Dimension	Tolerance
L	3.5	+/-0.2
W	2.8	+/-0.2
H	1.9	+/-0.2
F	2.2	+/-0.1
S	0.8	+0.2/-0.3
B	0.4	+/-0.15
X	0.1	+/-0.1
P	0.5	REF
R	1	REF
T	0.13	REF
A	1.9	MIN
G	1.8	REF
E	2.2	REF

Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	2000

General Information

Supplier:	KEMET
Application:	Low ESR
Part Type Description:	SMD, MnO ₂ , Molded, Low ESR
Construction:	Standard Chip-MnO ₂
Body Type:	SMD Chip
Footprint:	3528
Weight:	107.45 mg
RoHS:	Yes

Specifications

Capacitance:	22 uF
Tolerance:	+/-20%
Voltage:	10 VDC (85C)
Voltage:	6.7 VDC (125C)
Temperature Range:	-55/+125C
Current/Ripple Current:	348 mAmps (25C)
Current/Ripple Current:	313.2 mAmps (85C)
Current/Ripple Current:	139.2 mAmps (125C)
Resistance/ESR:	0.7 Ohms (100kHz)
Failure Rate:	N/A
Leakage Current:	2.2 uA
Dissipation Factor:	6%