

KEMET Part Number: T495C336K016ATE300
(B45197A3336K309)

Capacitor, Tantalum, SMD, MnO₂, Molded, Low ESR, 33 uF, 6032, +/-10% Tol, 16 VDC (85C)



Dimensions (mm)

Symbol	Dimension	Tolerance
L	6	+/-0.3
W	3.2	+/-0.3
H	2.5	+/-0.3
F	2.2	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	0.9	REF
R	1	REF
T	0.13	REF
A	2.9	MIN
G	2.8	REF
E	2.4	REF

Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500

General Information

Supplier:	KEMET
Application:	Low ESR
Part Type Description:	SMD, MnO ₂ , Molded, Low ESR
Construction:	Standard Chip-MnO ₂
Body Type:	SMD Chip
Footprint:	6032
Weight:	224.48 mg
RoHS:	Yes

Specifications

Capacitance:	33 uF
Tolerance:	+/-10%
Voltage:	16 VDC (85C)
Voltage:	10.72 VDC (125C)
Temperature Range:	-55/+125C
Current/Ripple Current:	606 mAmps (25C)
Current/Ripple Current:	545.4 mAmps (85C)
Current/Ripple Current:	242.4 mAmps (125C)
Resistance/ESR:	300 mOhms (100kHz)
Failure Rate:	N/A
Leakage Current:	5.3 uA
Dissipation Factor:	6%