



# QVIS® | 4MP IP EYEBALL CAMERA

Superior Image quality • Switchable H.264 / H.265

## FEATURES:

- Up to 4 mega pixel high resolution
- Wide dynamic Range
- Privacy masking
- Day and night
- Dual video streams
- Plug and Play with all Qvis NVR's
- 4MP@15FPS
- 3D Digital Noise Reduction
- DC12V & PoE
- IR cut filter
- Onvif 2.4
- IP67 weather-proof protection
- Supports both H.264 and H.265  
H265 Twice the compression  
using half the hard drive storage
- Superior Image quality

## RECOMMENDED NVR:

Click here to find out more



| SPECIFICATION               |  | EYE-4MP-FG/W   |
|-----------------------------|--|--|
| <b>CAMERA</b>               |  |  |
| Image Sensor                | 1/3" Progressive Scan CMOS Sensor  |  |
| Min illumination            | 0.05 Lux (F1.2), 0 Lux (IR on)   |  |
| Shutter time                | Auto, 1/25 ~ 1/10000s  |  |
| Lens                        | 3.6mm  |  |
| Lens Mount                  | M12  |  |
| Day & Night                 | IR cut filter with auto switch   |  |
| Wide Dynamic Range          | >80dB  |  |
| Digital noise Reduction     | 3D NR  |  |
| S/N Ratio                   | ≥50db(AGC OFF)   |  |
| Privacy Masking             | Up to 4 areas  |  |
| <b>COMPRESSION STANDARD</b> |  |  |
| Video Compression           | H.264/H.265 & MJPEG  |  |
| H.265 code profile          | Main Profile   |  |
| Video bit rate              | 32KB ~16Mbps, support VBR, CBR   |  |
| Dual Stream                 | Dual-stream encoding   |  |
| <b>VIDEO</b>                |  |  |
| Max Image Resolution        | 2688 x 1520  |  |
| Resolution                  | 2592*1520/2048*1520/1080P(1920×1080)/<br>D1(704×576)/VGA(640*480)/QVGA(320×240)  |  |
| Frame Rate                  | Main Stream  | 2592*1520(1~15fps);<br>2048*1520/1080P(1 ~ 25/30fps) |
|                             | Sub Stream   | D1/VGA/QVGA(1 ~ 25/30fps)                            |
| <b>NETWORK</b>              |  |  |
| Network Storage             | Video record, Picture format   |  |
| Alarm Trigger               | Manual, Automatic (motion detection, alarm, schedule, cycle)                     |  |
| Protocols                   | TCP/IP, UDP, RTP, RTSP, RTCP, HTTP, DNS, DDNS, DHCP, FTP, NTP, PPPOE, SMTP, UPNP |  |
| Alarm data transmission     | FTP, E-mail, Browser, CMS  |  |
| System Compatibility        | ONVIF 2.4  |  |
| <b>INTERFACE</b>            |  |  |
| Communication Interface     | 1 RJ45 10M/100M Ethernet interface   |  |
| <b>GENERAL</b>              |  |  |
| Operating Conditions        | -20°C~+55°C , Less than 90% RH   |  |
| Power Supply                | DC12V / PoE (802.3af)  |  |
| Power Consumption           | <3W  |  |
| Weather Proof               | IP67   |  |
| IR Range                    | Up to 30M  |  |
| Dimensions                  | Φ105.5mm*75.5mm  |  |
| Weight                      | 500gms   |  |
| Max. User Access            | 8/20 users, IE, Google, Firefox  |  |
| Smart Phone                 | iPhone, iPad, Android  |  |