



- 316L SS Pressure Sensor with PVC Threads
- Small Profile
- 4.5V (typ) High Level Output
- Gage, Absolute, Sealed Gage
- ASIC Calibrated
- Variety of Cable Lengths

### DESCRIPTION

The LM incorporates stainless steel and plastic isolation suitable for level sensing in water and other liquids. The LM uses a patented low cost stainless steel sensor in a PVC plastic fitting. The modular design is adaptable to an infinite number of plastic port variations. With high performance in a small form factor, the LM Series enables the miniaturization of high accuracy pressure systems. The standard output is 4.5V with a 5V supply.

### **FEATURES**

## **APPLICATIONS**

- Threaded Process Fitting
- -20°C to +70°C Operating Temperature
- ±1% Accuracy
- ±3.0% Total Error Band
- Solid State Reliability
- Variety of Cable Lengths

- Irrigation
- RV and Marine Holding Tank Level
- Water Storage & Recycling Systems
- Small Tank Fluid Level
- Chillers & Evaporative Coolers

## **STANDARD RANGES**

Range (psi)	Range (Bar)	Gage	Absolute	Sealed Gage
0 to 1	0 to .07	•		
0 to 2	0 to .20	•		
0 to 5	0 to .35	•	•	•
0 to 15	0 to 1	•	•	•
0 to 30	0 to 2	•	•	•
0 to 50	0 to 5	•	•	•
0 to 100	0 to 7	•	•	•
0 to 150	0 to 10	•	•	•

Note: Intermediate pressure ranges available.

# PERFORMANCE SPECIFICATIONS

Supply Voltage: 5.0Vdc

Ambient Temperature: 25°C (unless otherwise specified)

PARAMETERS	MIN	ТҮР	МАХ	UNITS	NOTES	
Full Scale Output		4.5		V	1	
Zero Pressure Output		0.5		V	1, 2	
Accuracy (combined linearity, hysteresis, & repeatability)	-1		+1	%Span	3	
Total Error Band (includes calibration errors						
above & temperature effects over the compensated range)	-3		+3	%Span		
Supply Voltage	4.75	5.00	5.25	V		
Insulation Resistance (50Vdc)	50			MΩ	4	
Pressure Overload			3X	Rated	5	
Pressure Burst			4X	Rated	6	
Compensated Temperature	0		40	°C		
Operating Temperature	-20		+70	°C		
Tightening Torque (recommended)	1~2 Turns fro	m Finger Tight			7	
Zero Offset Effect @ 1psiG from 90° Changes due to Installation Orientation		0.6		%Span	8	
Media, Pressure Port Liquids and Gases compatible with PVC, 316/316L ST STL, Buna-N O-Ring						

#### Notes

1. Ratiometric to supply voltage.


- 2. Measured at vacuum for Absolute (A), ambient for Gage (G) and Sealed Gage (S).
- 3. Best fit straight line.
- 4. Minimum from any wire to metal diaphragm.
- 5. The maximum pressure that can be applied without changing the transducer's performance or accuracy
- 6. The maximum pressure that can be applied to a transducer without rupture of either the sensing element or transducer.
- 7. Over-torquing will damage the PVC fitting and will cause sensor calibration and/or zero offset to shift during installation. Always check for a zero offset shift after installing.
- 8. Zero offset effect is inversely ratiometric to pressure range, for 2psiG: 0.3% Span (typ); for 5psiG: 0.12% Span (typ).

#### **Additional Notes**

- 9. Standard gage units are not recommended for vacuum applications.
- 10. Direct mechanical contact with diaphragm is prohibited. Diaphragm surface must remain free of defects (scratches, punctures, dents, fingerprints, etc.) for device to operate properly. Caution is advised when handling parts with exposed diaphragms. Use protective cap whenever devices are not in use.



# DIMENSIONS



ALL DIMENSIONS IN INCHESEMN]



# **ORDERING INFORMATION**

LM	3	1	-	00000	F	-	100	P	G
Model	Output Signal	Connection Type	-	00000	Pressure Port	-	Pressure Range		Pressure Type
LM	3* = 0.5 − 4.5V Ratiometric X = Special	Dim 'L' Cable Inches [mm] $1 = 12 \pm 0.25 [305 \pm 6.4]$ $2 = 24 \pm 0.5 [610 \pm 12.7]$ $3 = 48 \pm 1.0 [1219 \pm 25.4]$ $4 = 84 \pm 1.5 [2134 \pm 38.1]$ $5 = 120 \pm 1.5 [3048 \pm 38.1]$ $6 = 180 \pm 2.0 [4572 \pm 50.8]$ $7 = 360 \pm 2.0 [9144 \pm 50.8]$	-	00000	<b>F</b> = 1/2-14 NPT <b>X</b> = Special	-	001P** 002P** 005P 015P 030P 050P 100P 150P	.07B** .20B** .35B 001B 002B 005B 005B 007B 010B	<b>G</b> = Gage <b>A</b> = Absolute <b>S</b> = Sealed Gage

\*Note: Ratiometric output span changes with input voltage. (See supply voltage specification) \*\*Note: 1psi (.07Bar) and 2psi (.20Bar) only available in Gage (G). (See standard rages)

### NORTH AMERICA

Measurement Specialties 45738 Northport Loop West Fremont, CA 94538 Tel: 1-800-767-1888 Fax: 1-510-498-1578 Sales: pfg.cs.amer@meas-spec.com

### EUROPE

Measurement Specialties (Europe), Ltd. 26 Rue des Dames 78340 Les Clayes-sous-Bois, France Tel: +33 (0) 130 79 33 00 Fax: +33 (0) 134 81 03 59 Sales: pfg.cs.emea@meas-spec.com

### ASIA

Measurement Specialties (China), Ltd. No. 26 Langshan Road Shenzhen High-Tech Park (North) Nanshan District, Shenzhen 518057 China Tel: +86 755 3330 5088 Fax: +86 755 3330 5099 Sales: pfg.cs.asia@meas-spec.com

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.