

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**SECTION 1: Identification of the substance/mixture and of the company/undertaking**

· **1.1 Product identifier**

· **Trade name:** *Window cleaner concentrate RM 503*

· **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
*No further relevant information available.*

· **Application of the substance / the mixture** *Detergent*

· **1.3 Details of the supplier of the safety data sheet**

· **Manufacturer/Supplier:**

*Alfred Kärcher GmbH & Co. KG  
Alfred-Kärcher-Str. 28-40  
D - 71364 Winnenden*

*Postfach 160  
D - 71349 Winnenden*

*Tel.: +49-7195-14-0  
Fax : +49-7195-14-2212*

*www.karcher.com*

· **Further information obtainable from:**

*Department PDE-D*

*Tel.: +49-7195-14-2398*

*Fax : +49-7195-14-3164*

*safetydata@karcher.com*

· **1.4 Emergency telephone number:** *Tel.: 0049 30 30686 790 Giftnotruf Berlin*

**SECTION 2: Hazards identification**

· **2.1 Classification of the substance or mixture**

· **Classification according to Regulation (EC) No 1272/2008**

*Eye Irrit. 2 H319 Causes serious eye irritation.*

· **2.2 Label elements**

· **Labelling according to Regulation (EC) No 1272/2008**

*The product is classified and labelled according to the CLP regulation.*

· **Hazard pictograms**



GHS07

· **Signal word** *Warning*

· **Hazard statements**

*H319 Causes serious eye irritation.*

· **Precautionary statements**

*P102 Keep out of reach of children.*

*P280 Wear eye protection / face protection.*

(Contd. on page 2)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**Trade name: Window cleaner concentrate RM 503**

(Contd. of page 1)

- P264 Wash hands thoroughly after handling.  
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
 P337+P313 If eye irritation persists: Get medical advice/attention.

- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

**SECTION 3: Composition/information on ingredients**

- **3.2 Chemical characterisation: Mixtures**
- **Description:**  
Mixture of substances listed below with non-hazardous additions.  
Cleaning agent

· **Dangerous components:**

CAS: 107-98-2 EINECS: 203-539-1 Index number: 603-064-00-3 Reg.nr.: 01-2119457435-35-XXXX	1-methoxypropan-2-ol ⚠ Flam. Liq. 3, H226; ⚠ STOT SE 3, H336	≤10%
CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 02-2119752543-38-XXXX	propan-2-ol ⚠ Flam. Liq. 2, H225; ⚠ Eye Irrit. 2, H319; STOT SE 3, H336	≤10%
CAS: 2605-79-0 EINECS: 220-020-5	decyldimethyl aminoxide ⚠ Eye Dam. 1, H318; ⚠ Aquatic Acute 1, H400; Aquatic Chronic 2, H411; ⚠ Acute Tox. 4, H302; Skin Irrit. 2, H315	0,1-<1%

· **Regulation (EC) No 648/2004 on detergents / Labelling for contents**

cationic surfactants, non-ionic surfactants < 5%

- **Additional information** For the wording of the listed risk phrases refer to section 16.

**SECTION 4: First aid measures**

- **4.1 Description of first aid measures**
- **After inhalation** Supply fresh air; consult doctor in case of complaints.
- **After skin contact** Generally the product does not irritate the skin.
- **After eye contact** Rinse opened eye for several minutes under running water.
- **After swallowing**  
Rinse out mouth and then drink plenty of water.  
If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed**  
No further relevant information available.

(Contd. on page 3)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**Trade name: Window cleaner concentrate RM 503**

(Contd. of page 2)

- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

### **SECTION 5: Firefighting measures**

- **5.1 Extinguishing media**
- **Suitable extinguishing agents**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents** Water with full jet.
- **5.2 Special hazards arising from the substance or mixture**  
No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

### **SECTION 6: Accidental release measures**

- **6.1 Personal precautions, protective equipment and emergency procedures** Not required.
- **6.2 Environmental precautions:**  
Dilute with plenty of water.  
Do not allow to enter sewers/ surface or ground water.  
Do not allow to penetrate the ground/soil.
- **6.3 Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders).  
Ensure adequate ventilation.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

\*

### **SECTION 7: Handling and storage**

- **7.1 Precautions for safe handling**  
Ensure good ventilation/exhaustion at the workplace.  
Prevent formation of aerosols.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Storage class** VCI storage class: 12
- **7.3 Specific end use(s)** No further relevant information available.

\*

### **SECTION 8: Exposure controls/personal protection**

- **Additional information about design of technical facilities:** No further data; see item 7.

(Contd. on page 4)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**Trade name: Window cleaner concentrate RM 503**

(Contd. of page 3)

· **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

**107-98-2 1-methoxypropan-2-ol**

<b>IOELV</b>	Short-term value: 568 mg/m <sup>3</sup> , 150 ppm Long-term value: 375 mg/m <sup>3</sup> , 100 ppm Skin
--------------	---

· **DNELs**

**67-63-0 propan-2-ol**

<b>Oral</b>	<b>DNEL</b>	26 mg/kg*d (consumer)
<b>Dermal</b>	<b>DNEL</b>	888 mg/kg*d (employee) 319 mg/kg*d (consumer)
<b>Inhalative</b>	<b>DNEL</b>	500 mg/m <sup>3</sup> (employee) 89 mg/m <sup>3</sup> (consumer)

· **8.2 Exposure controls**

· **Personal protective equipment**

· **General protective and hygienic measures**

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

· **Respiratory protection:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

Not necessary if room is well-ventilated.

· **Protection of hands:** Not required.

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles.

**SECTION 9: Physical and chemical properties**

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

**Form:** Fluid

(Contd. on page 5)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**Trade name: Window cleaner concentrate RM 503**

(Contd. of page 4)

· <b>Colour:</b>	Yellow
· <b>Odour:</b>	citrus-like
· <b>Odour threshold:</b>	Not determined.
· <b>pH-value at 20 °C:</b>	5,4
· <b>pH-value 1 %:</b>	5
· <b>Change in condition</b>	
<b>Melting point/Melting range:</b>	-5 °C
<b>Boiling point/Boiling range:</b>	100 °C
· <b>Flash point:</b>	37 °C
· <b>Flammability (solid, gaseous)</b>	Not applicable.
· <b>Ignition temperature:</b>	not applicable
· <b>Decomposition temperature:</b>	Not determined.
· <b>Self-igniting:</b>	Product is not selfigniting.
· <b>Danger of explosion:</b>	Product does not present an explosion hazard.
· <b>Explosion limits:</b>	
<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.
· <b>Vapour pressure at 20 °C:</b>	43 hPa
· <b>Density at 20 °C:</b>	0,984 g/cm <sup>3</sup>
· <b>Relative density</b>	Not determined.
· <b>Vapour density</b>	Not determined.
· <b>Evaporation rate</b>	Not determined.
· <b>Solubility in / Miscibility with Water:</b>	Fully miscible
· <b>Partition coefficient (n-octanol/water):</b>	Not determined.
· <b>Viscosity:</b>	
<b>dynamic at 20 °C:</b>	3 mPas
<b>kinematic:</b>	Not determined.
· <b>Solvent content:</b>	
<b>Organic solvents:</b>	20,0 %
<b>VOC (EC)</b>	20,00 %
<b>Solids content:</b>	2,1 %
· <b>9.2 Other information</b>	No further relevant information available.
· <b>Additional information</b>	Does not support burning

**SECTION 10: Stability and reactivity**

· 10.1 Reactivity corresponds to 10.3

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**Trade name: Window cleaner concentrate RM 503**

(Contd. of page 5)

- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known

**SECTION 11: Toxicological information**

- **11.1 Information on toxicological effects**
- **Acute toxicity**

- **LD/LC50 values relevant for classification:**

**107-98-2 1-methoxypropan-2-ol**

Dermal	LD50	> 2000 mg/kg (rbt)
Inhalative	LC50	4016 mg/kg (Rat)
	LC50/4 h	6 mg/l (Rat)

**67-63-0 propan-2-ol**

Dermal	LD50	12800 mg/kg (can)
		12800 mg/kg (rabbit)
Inhalative	LC50	5280 mg/kg (Rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation**  
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

**SECTION 12: Ecological information**

- **12.1 Toxicity**

- **Aquatic toxicity:**

**67-63-0 propan-2-ol**

EC10/18 h	> 1000 mg/l (Pseudomonas putida) (DIN 38412)
EC50/48 h	13299 mg/l (Daphnia magna)
EC50/72 h	> 1000 mg/l (Desmodesmus subspicatus)
LC50/96 h	9640 mg/l (Pimephales promelas)

- **12.2 Persistence and degradability** No further relevant information available.

(Contd. on page 7)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**Trade name: Window cleaner concentrate RM 503**

(Contd. of page 6)

- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **CSB-value:** 526.000 mg/l
- **General notes:**  
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

### SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
  - **Recommendation**  
Must not be disposed together with household garbage. Do not allow product to reach sewage system.  
Must be specially treated adhering to official regulations.
- |  |
|--|
| · <b>European waste catalogue</b>                    |
| 07 06 01* aqueous washing liquids and mother liquors |
- **Uncleaned packaging:**
  - **Recommendation:** Non contaminated packagings may be recycled.
  - **Recommended cleansing agents:** Water, if necessary together with cleaning agents.

### SECTION 14: Transport information

- |  |                 |
|--|-----------------|
| · <b>14.1 UN-Number</b>  |                 |
| · <b>ADR, ADN, IMDG, IATA</b>  | Void            |
| · <b>14.2 UN proper shipping name</b>  |                 |
| · <b>ADR, ADN, IMDG, IATA</b>  | Void            |
| · <b>14.3 Transport hazard class(es)</b>   |                 |
| · <b>ADR, ADN, IMDG, IATA</b>  |                 |
| · <b>Class</b>   | Void            |
| · <b>14.4 Packing group</b>  |                 |
| · <b>ADR, IMDG, IATA</b>   | Void            |
| · <b>14.5 Environmental hazards:</b>   |                 |
| · <b>Marine pollutant:</b>   | No              |
| · <b>14.6 Special precautions for user</b>                                       | Not applicable. |
| · <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b> | Not applicable. |

(Contd. on page 8)



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Page 8/9  
**KÄRCHER**

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**Trade name: Window cleaner concentrate RM 503**

(Contd. of page 7)

· **UN "Model Regulation":** Void

**SECTION 15: Regulatory information**

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **National regulations**
- **Information about limitation of use:**  
Employment restrictions concerning juveniles must be observed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

**SECTION 16: Other information**

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship. A product information sheet can be provided if requested.*

- **Relevant phrases**  
H225 Highly flammable liquid and vapour.  
H226 Flammable liquid and vapour.  
H302 Harmful if swallowed.  
H315 Causes skin irritation.  
H318 Causes serious eye damage.  
H319 Causes serious eye irritation.  
H336 May cause drowsiness or dizziness.  
H400 Very toxic to aquatic life.  
H411 Toxic to aquatic life with long lasting effects.
- **Department issuing MSDS:** PCD-D
- **Contact:**  
Department PDE-D  
Tel.: +49-7195-14-2398  
Fax : +49-7195-14-3164  
safetydata@karcher.com
- **Abbreviations and acronyms:**  
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)  
IMDG: International Maritime Code for Dangerous Goods  
IATA: International Air Transport Association  
GHS: Globally Harmonised System of Classification and Labelling of Chemicals  
EINECS: European Inventory of Existing Commercial Chemical Substances  
ELINCS: European List of Notified Chemical Substances  
CAS: Chemical Abstracts Service (division of the American Chemical Society)  
VOC: Volatile Organic Compounds (USA, EU)  
DNEL: Derived No-Effect Level (REACH)  
LC50: Lethal concentration, 50 percent  
LD50: Lethal dose, 50 percent  
PBT: Persistent, Bioaccumulative and Toxic  
vPvB: very Persistent and very Bioaccumulative

(Contd. on page 9)

EU



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 09.10.2015

Version number 2

Revision: 18.12.2014

**Trade name: Window cleaner concentrate RM 503**

(Contd. of page 8)

*Flam. Liq. 2: Flammable liquids, Hazard Category 2*  
*Flam. Liq. 3: Flammable liquids, Hazard Category 3*  
*Acute Tox. 4: Acute toxicity, Hazard Category 4*  
*Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2*  
*Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1*  
*Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2*  
*STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3*  
*Aquatic Acute 1: Hazardous to the aquatic environment - Acute Hazard, Category 1*  
*Aquatic Chronic 2: Hazardous to the aquatic environment - Chronic Hazard, Category 2*  
· **\* Data compared to the previous version altered.**

· 0.011-372.0                      RM 503/5.1                      1.841

EU